



The Energizer® Clip Light is a compact and versatile lighting option. It can be clipped to multiple surfaces and in different orientations such as backpacks, clothing, and books. The Light Fusion Technology provides a powerful and uniform light output making this light a good hands-free solution for various indoor and outdoor activities. In addition to the white LED, it also has a red LED and flashing red LED that can be used to preserve night vision and provide visibility for safety.

Lumens	Runtime	Beam Distance	Drop	Water Ingress



DESIGN BENEFITS
✓ Durable Plastic Construction
✓ Built-in Clip for various hands-free usages
✓ Red LED for night vision and Red Flashing for visibility and emergency
✓ Compact and lightweight design allow for ease of use

PERFORMANCE BENEFITS
✓ Light Fusion Technology for powerful and uniform light output
✓ Long Run Time

LIGHT AND POWER SOURCE
✓ Features LED Technology
✓ Operates on 2 x CR2032 Energizer® Coin Cells

PRODUCT SPECIFICATIONS
Weight: 17 Grams / 0.61 Ounces
Dimensions: 60 mm x 33 mm x 20 mm 2.33" x 1.30" x 0.76"

BATTERY SPECIFICATIONS	
Battery Type	Energizer Coin Cells
Battery Size	CR2032
Number of Cells	2

BATTERY PERFORMANCE			
Modes	Lumens (lm)	Runtime (h)	Beam Distance (m)
On	30	3h 15m	-
Red	-	-	-
Flashing Red	-	-	-

Modes
On, Red, Red Flashing

ELECTRICAL CHARACTERISTICS
Nominal Power Consumption: xx W
Batteries: 2 CR2032 Energizer Coin Cells
LED Specifications: LED 3.0V cc / xxx mA

DISCLAIMERS
Tested according to ANSI FL1 Standards.
This device complies with part 15 of the FCC Rules.
Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.
*Light output measured from LED. Value is only applicable to the LED. Actual device light output may vary.
**Endpoint determined at 1% of initial value.

CERTIFICATES AND COMPLIANCE
EMC, EN62471, FCC

Publish Date: DD-MM-YYYY

OPERATING INSTRUCTIONS

1. Press on/off button to turn on.
2. Press 1x for white.
3. Press 2x for red.
4. Press 3x for red flashing.
5. Press again to turn off.

BATTERY CHANGING INSTRUCTIONS

1. Using a small screwdriver unscrew the small screws.
2. Remove cover
3. Replace batteries according to the diagram inside.
4. Replace cover and tighten all screws.