


PXMBNI23FPM12ASC Datasheet

**Product Name // M23 Series A Code Brass Nickel Plated
M20 Front Panel Mount Connector 12 Contact Pins**

[View Product Page](#)



// Product Description:

- ⊕ M23 Series Panel Mount Connectors
- ⊕ Water and dustproof to IP67 when mated with compatible connector
- ⊕ A Code
- ⊕ Front Panel Mount
- ⊕ 12, 19 Contact
- ⊕ Solder Terminals
- ⊕ Mate with M23 Series Inline Body and Flex Body Connectors, depending on part code

// General Information:

Product Display Title:	M23 Series Panel Mount Connectors
Product Family:	Circular Automation Connectors
Product Series:	M23 Series
Change Notes:	PRODUCT-MOQ-ADJUSTMENT
Body Material:	Brass - Nickel Plated
Contact Type:	Plug Contact
Coupling Type:	Screw
Current Max:	8A
Diameter Over Coupling Ring Mm:	26mm
Function:	Front Panel Mount Connector
Ip Rating:	IP67
M12 Series Mounting Nut:	M20
Max Operating Temperature:	+80°C
Min Operating Temperature:	-25°C
Number Of Contacts:	12 Contacts
Pin Layout Code:	A Code
Thread Size:	M23 x 1
Voltage Max:	200V

// Product PDF Links

[M23 Series automation connectors...](#)

// Product 3D CAD Model Links

[PXMBNI23FPM12ASC3D CAD Model](#)