Buccaneer 400 Series Environmentally Sealed Connector

SPECIFICATION

Electrical:

Poles:	2, 3	4, 6, 8	10, 12	
Current Rating:	8A	5A	1A	
Voltage Rating:	250V	125V	50V	
Contact Resistance:	$<\!5$ m Ω			
Insulation Resistance:	>10 ⁶ MΩ (@ 500V a.c.)			
AC Breakdown Voltage:	2.5kV			
Operating Temperature Range: Approvals:	-40° to +80°C UL, CSA & VDE			

Mechanical:

Sealing:	IP68, EN 60529						
Cable Acceptance:	3.0 - 7.0mm						
Contact Accommodation:	2, 3 pole, 20 - 24 AWG 4, 6, 8 pole, 22 - 26 AWG 10, 12 pole, 24 - 28 AWG						
Termination:	Crimp, solder and PCB						
Insertion/Withrawal Force:							
No. poles:	2	3	4	6	8	10	12
Insertion Force (typ):	19N	25N	27N	27N	28N	55N	62N
Withdrawal Force (typ):	12N	17N	17N	21N	22N	25N	29N
Cable Retention force:	80N						


Dimensions:

Overall dimensions of connecto	rs when mated together
Flex + Flex In-Line	80mm
Dia. over coupling ring	19.1mm

Material:

Body Mouldings:	Polyamide
Flammibilty Rating:	UL94V-0
UV Resistance:	To EN 50021:1999
Contacts:	Copper alloy, Gold plated
O Rings:	Nitrile
Chassis Sealing O Ring:	Nitrile
RoHS	Compliant

Caution: Not for interrupting current Attention: Ne pas utiliser pour couper le courant



Plug

Socket

400 Series Buccaneer

IP68 Sealed Electrical Cable Connectors

Wiring and Assembly Instructions



www.bulgin.co.uk

Green/Yellow to terminal E

Buccaneer 400 Series Environmentally Sealed Connectors

