

Fingertip size: 20.1 × 12.5 × 10.1 mm

OTON IS OUR BUSINESS

- → Weight: 5 g
- Spectral response range: 340 to 780 nm
- Spectral resolution: 15 nm max.
- Hermetic package: High reliability against humidity
- Installation into mobile measurement equipment
- Wavelength conversion factor*1 is listed on final inspection sheet

Mini-spectrometer

Micro series

C12666MA

Fingertip size, ultra-compact spectrometer head integrating MEMS and image sensor technologies

The C12666MA is an ultra-compact (Fingertip size) spectrometer head developed based on our MEMS and image sensor technologies. The adoption of a newly designed optical system has achieved a remarkably small size, less than half the volume of the previous mini-spectrometer MS series (C10988MA-01). In addition, the employment of hermetic packaging has improved humidity resistance.

This product is suitable for integration into a variety of devices, such as integration into printers and hand-held color monitoring devices that require color management. It is also suitable for applications that collaborate with portable devices, such as smartphones and tablets.

- Applications

- Color monitoring for printers and printing machines
- Testers for lights and LEDs
- Color adjustment of various large size displays
- Water quality control monitors and other environment measuring instruments
- Measuring instruments that use portable devices such as smartphones and tablets
- *1: A conversion factor for converting the image sensor pixel number into a wavelength. A calculation factor for converting the A/D converted count into the input light level is not provided.

Optical characteristics

Parameter		Value	Unit	
Spectral response range		340 to 780	nm	
Sportral resolution (FW/HM)	Тур.	12		
Spectral resolution (FWHM)	Max.	15	nm	
Wavelength reproducibility*2		-0.5 to +0.5	nm	
Wavelength temperature dep	endence	-0.1 to +0.1	nm/°C	
Spectral stray light*3		-25	dB	

*2: Measured under constant light input conditions

*3: Spectral stray light = $10 \times \log (TI/Th)$

Th: output signal when a light spectrum at a certain wavelength is input

TI: output signal at that wavelength \pm 40 nm

Electrical characteristics

Parameter	Min.	Тур.	Max.	Unit
Supply voltage	4.75	5	5.25	V
Power consumption	-	30	-	mW
Video rate	0.25	-	200	kHz
Output impedance	-	150 *4	-	Ω

*4: An increase in the current consumption at the video output terminal also increases the chip temperature and so causes the dark current to rise. To avoid this, connect a buffer amplifier for impedance conversion to the video output terminal so that the current flow is minimized. As the buffer amplifier, use a JFET or CMOS input operational amplifier of optical input impedance.

Structure

Parameter Specification		Unit
Dimensions (W \times D \times H)	20.1 × 12.5 × 10.1	
Weight	5	g
Slit ^{*5} (H \times V)	50 × 750	μm
NA*6	0.22	-
Image sensor (H × V)	CMOS linear image sensor with a slit	-
Number of pixels	256	pixels
Pixel size (H \times V)	12.5 × 1000	μm

*5: Entrance slit aperture size

*6: Numeric aperture (solid angle)

Absolute maximum ratings

Parameter	Value	Unit
Operating temperature*7	+5 to +50	°C
Storage temperature*7	-20 to +70	°C

*7: No dew condensation


When there is a temperature difference between a product and the surrounding area in high humidity environment, dew condensation may occur on the product surface. Dew condensation on the product may cause deterioration in characteristics and reliability. Note: Exceeding the absolute maximum ratings even momentarily may cause a drop in product quality. Always be sure to use the product within the shealute maximum ratings.

within the absolute maximum ratings.

Optical component layout


Besides a CMOS image sensor chip integrated with an optical slit by etching technology, the C12666MA employs a reflective concave blazed grating formed by nanoimprint. In addition, the glass used in the light path of the previous C10988MA-01 is not used in the C12666MA, making it extremely compact.

▷ Structure






CMOS linear image sensor with a slit [Incident light side (back of chip)]






Spectral resolution vs. wavelength (typical example)



Spectral response (typical example)




Dark output vs. ambient temperature (typical example)



KACCB0352EC

PHOTON IS OUR BUSINESS

Measurable incident light level




* Input spot diameter: 800 μ m (λ =550 nm)

KACCB354EA

4

Recommended driver circuit example




Precautions

- The packaging of C12666MA is electrically conductive, so be careful when designing the circuit to avoid short circuit caused by contact with a circuit pattern.
- \cdot If external force is repeatedly applied to the lead pins, this may damage the lead pins.
- \cdot To prevent damage due to soldering, be careful of the soldering temperature and time.
- As a general guide, finish soldering within 3.5 seconds at 350 °C or less when soldering by hand, or within 10 seconds at 260 °C or less when using a solder bath.



Dimensional outline

(unit: mm, tolerance unless otherwise noted: ±0.2)



Pin connections

Make electrical connections to an external circuit using leads.

Pin no.	Symbol	Name	I/O	Description
1	Vdd	Supply voltage	I	Image sensor power supply: 5 V
2	Video	Video output	0	Video output signal
3	GND	Ground	-	Sensor ground
4	CLK	Clock pulse	I	Sensor scan sync signal
5	Case	Case	-	Case connection terminal
6	NC		-	No connection
7	ST	Start pulse	I	Start pulse
8	NC		-	No connection
9	Gain	Gain	I	Image sensor: Gain setting
10	EOS	End of scan	0	Sensor scan end signal


Note: Pin no. 9 is pulled up internally to Vdd via 10 k Ω .

Do not pull-up or pull-down the gain setting using an external circuit. For low gain, leave the pin open or connect to Vdd. For high gain, connect to GND.

a mamatsu

PHOTON IS OUR BUSINESS

Enlarged view of slit (unit: mm)



5

Internal CMOS image sensor specifications

Recommended terminal voltage

Parameter		Symbol	Min.	Тур.	Max.	Unit
Supply voltage		Vdd	4.75	5	5.25	V
Gain selection terminal	High gain	Gain	0	-	0.4	V
voltage	Low gain	Gain	Vdd - 0.25	Vdd	Vdd + 0.25	V
Clock pulse voltage	High level		Vdd - 0.25	Vdd	Vdd + 0.25	V
	Low level	V(CLK)	0	-	0.4	V
Start pulse voltage	High level	V(ST)	Vdd - 0.25	Vdd	Vdd + 0.25	V
	Low level	v(SI)	0	-	0.4	V

Electrical characteristics [Ta=25 °C, Vdd=5 V, V(CLK)=V(ST)=5 V]

Parameter		Symbol	Min.	Тур.	Max.	Unit
Clock pulse frequency		f(CLK)	1	-	800	kHz
Device concurrention	High gain	P	-	-	60	m\\/
Power consumption	Low gain		-	-	60	mW


Electrical and optical characteristics [Ta=25 °C, Vdd=5 V, V(CLK)=V(ST)=5 V]

Parameter		Symbol	Min.	Тур.	Max.	Unit
Dark current	High gain	ID	-	0.02	0.08	
	Low gain		-	0.02	0.08	рА
Output offset voltage	High gain	Vo	0.15	0.35	0.55	v
	Low gain	VO	0.15	0.35	0.55	v
Charge amplifier feedback	High gain	Cf	-	1.4	-	pF
capacitance*8	Low gain		-	4.8	-	
Saturation output voltago*9	High gain	Vsat	2.3	2.8	3.3	v
Saturation output voltage*9	Low gain	vsat	1.4	1.7	2.0	V
Readout noise	High gain	Nr	-	0.3	0.5	mV rms
	Low gain		-	0.2	0.4	

*8: Gain=5 V (low gain), Vg=0 V (high gain) *9: Voltage difference relative to Vo



Timing chart



Parameter	Symbol	Min.	Тур.	Max.	Unit
Start pulse high period	thw(ST)	1030/f(CLK)	-	-	S
Start pulse rise/fall times	tr(ST), tf(ST)	0	20	30	ns
Clock pulse duty ratio	-	45	50	55	%
Clock pulse rise/fall times	tr(CLK), tf(CLK)	0	20	30	ns
Video delay time	tvd	-	20	-	ns

Note: The clock pulse should be set from high to low just once when the start pulse is low. The internal shift register starts operating at this timing.

The integration time is determined by the start pulse intervals. However, since the charge integration of each pixel is carried out between the signal readout of that pixel and the next signal readout of the same pixel, the start time of charge integration differs depending on each pixel. In addition, the next start pulse cannot be input until signal readout from all pixels is completed. Video output is 1/4 of the clock pulse frequency.



Mini-spectrometer evaluation circuit C14465-10 (sold separately)

The C14465-10 is a circuit board designed to simply evaluate the characteristics of the mini-spectrometer. The characteristics of the mini-spectrometer can be evaluated using the evaluation software by connecting the mini-spectrometer to a PC with a USB cable A9160 (AB type, sold separately)^{*10}.

F Features

- Initial evaluation circuit for mini-spectrometer*11
- Wavelength conversion factors of the mini-spectrometer can be input from a PC.^{*12}
- High A/D resolution (16-bit)
- USB powered
- *10: Compatible OS:

Microsoft Windows 8.1 Professional (32-bit, 64-bit) Microsoft Windows 10 Professional (32-bit, 64-bit)



- *11: The C14465-10 is a modified version of the C14465 evaluation circuit for the previous mini-spectrometer MS series (C10988MA-01, C11708MA). Only the sensor board has been modified. If you already have the C14465, you only have to purchase the C14465-03 (the sensor board for mini-spectrometers) to evaluate C12666MA mini-spectrometers.
- *12: A typical wavelength conversion factor is entered at the time of shipment of the C14465-10. To measure a spectrum with higher wavelength accuracy, it is necessary to input the wavelength conversion factor listed in the final inspection sheet that comes with each mini-spectrometer.

Note: Microsoft and Windows are registered trademarks of Microsoft Corporation in the United States and/or other countries.

Electrical characteristics

Parameter	Specification	Unit
Interface	USB 2.0	-
A/D conversion	16	bit
Clock pulse frequency	800	kHz
Video rate	200	kHz
Integration time	5 to 10000	ms

Structure

Parameter		Specification	Unit
Applicable spect	rometer	C12666MA	
Dimonsions	Control board	80 × 60	mm
Dimensions	Sensor board	30 × 44	mm

- Absolute maximum ratings

Parameter	Value	Unit
Operating temperature*13	+5 to +40	°C
Storage temperature*13	-20 to +70	°C


*13: No dew condensation

When there is a temperature difference between a product and the surrounding area in high humidity environment, dew condensation may occur on the product surface. Dew condensation on the product may cause deterioration in characteristics and reliability.


Note: Exceeding the absolute maximum ratings even momentarily may cause a drop in product quality. Always be sure to use the product within the absolute maximum ratings.



- Connection example



Evaluation software display example





Related information

www.hamamatsu.com/sp/ssd/doc_en.html

- Precautions
- Disclaimer

Technical information

Mini-spectrometers

Information described in this material is current as of December 2022.

Product specifications are subject to change without prior notice due to improvements or other reasons. This document has been carefully prepared and the information contained is believed to be accurate. In rare cases, however, there may be inaccuracies such as text errors. Before using these products, always contact us for the delivery specification sheet to check the latest specifications.

The product warranty is valid for one year after delivery and is limited to product repair or replacement for defects discovered and reported to us within that one year period. However, even if within the warranty period we accept absolutely no liability for any loss caused by natural disasters or improper product use. Copying or reprinting the contents described in this material in whole or in part is prohibited without our prior permission.



www.hamamatsu.com

HAMAMATSU PHOTONICS K.K., Solid State Division

1126-1 Ichino-cho, Higashi-ku, Hamamatsu City, 435-8558 Japan, Telephone: (81)53-434-3311, Fax: (81)53-434-5184

1126-1 IChInO-ChO, HIgaShI-KU, HamamatSU LUTY, 4:55-6558 Japan, Ietephione: (a)p35-47-511, rax. (b)p3-47-510 U.S.A.: HAMAMTSU CORPORATION: 360 Foothill Road, Bridgewater, NJ 08807, U.S.A.; Telephone: (a)908-231-0960, Fax: (b)908-231-1218 Gemany: HAMAMTSU PHOTONICS DEUTSCHLAND GMBH: Arzbergerstr. 10, 82211 Herrsching am Ammerse, Germany; Telephone: (4)8152-375-0, Fax: (4)98152-265-8 E-mail: info@hamamatsu.de France: HAMAMATSU PHOTONICS FARACE S.A.R.L.: 19 Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: (33)1 69 53 71 00, Fax: (33)1 69 53 71 10 E-mail: info@hamamatsu.fr United Kingdowi: HAMAMATSU PHOTONICS TS ALB.A.L: 19 Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: (4)1707-29488, Fax: (417)1707-325777 E-mail: info@hamamatsu.cf United Kingdowi: HAMAMATSU PHOTONICS NCH LIMTED: 2 Howard Court, 10 Tewin Road, Welwyn Garden City, Hertfordhire, AL7 18W, UK, Telephone: (4)1707-325777 E-mail: info@hamamatsu.ce Italy: HAMAMATSU PHOTONICS TALLA S.A.L.: Strada della Moia, 1 in to 20044 Ares (Wilano), Italy, Telephone: (40)8-509-031-01, Fax: (39)2-95 58 17 31, Famil: info@hamamatsu.e Italy: HAMAMATSU PHOTONICS TALLA S.A.L.: Strada della Moia, 1 in to 20044 Ares (Wilano), Italy, Telephone: (30)2 55 81 741 E-mail: info@hamamatsu.if China: HAMAMATSU PHOTONICS TALLA S.A.L.: Strada della Moia, 1 in to 2004 Ares (Wilano), Italy, Telephone: (30)2 55 81 741 E-mail: info@hamamatsu.if China: HAMAMATSU PHOTONICS TALLA S.A.L.: Strada della Moia, 1 in to 2004 Ares (Wilano), Italy, Telephone: (30)2 55 81 741 E-mail: info@hamamatsu.if China: HAMAMATSU PHOTONICS TALLA S.A.L.: Strada della Moia, 1 in to 2004 Ares (Wilano), Italy, Telephone: (30)2 55 81 741 E-mail: info@hamamatsu.if China: HAMAMATSU PHOTONICS TALLA S.A.L.: Strada della Moia, 1 in to 2004 Ares (Wilano), Italy, Telephone: (30)2 55 81 741 E-mail: info@hamamatsu.if China: HAMAMATSU PHOTONICS TALLA S.A.L.: Strada della Moia, 1 in to 2004 Ares (Wilano), Italy, Telephone: (86)10-6586-6006, Fax: (86)10-6586-6066