

OTi DALI 160/220-240/ 24 2CH DT6/8 G3

CV Power supplies with DALI



Product family features

- Dimmable via Touch DIM
- Available as single-channel or multi-channel with DT6 and DT8 in one device
- Dimming range: 0.1...100 % (for 50-80-160W) or 1...100 % (for 30W)
- Line frequency: 0 Hz | 50 Hz | 60 Hz

Product family benefits

- Intelligent power matching thanks to Smart power supply
- Form factor for mounting on the cove or in luminaires
- No stroboscopic effect thanks to patented high PWM frequency management (> 2 kHz)
- Suitable for installation in emergency lighting systems according to EN 60598-2-22
- DALI message detection "LED Module failure"
- IP rating: IP20

Areas of application

- Cove lighting, wall washer, corridor, handrail, luminous ceilings
- Suitable for use in luminaires of protection class I and II

Technical data

Electrical data

Nominal input voltage	220...240 V
Mains frequency	50/60 Hz
Input voltage AC	198...264 V
Total harmonic distortion	< 5 %
Power factor λ	0.92C...0.99
Efficiency in full-load	93% ¹⁾
Device power loss	11 W
Inrush current	57 A
Max. ECG no. on circuit breaker 10 A (B)	4
Max. ECG no. on circuit breaker 10 A (C)	8
Max. ECG no. on circuit breaker 16 A (B)	7
Max. ECG no. on circuit breaker 16 A (C)	13
Max. ECG no. on circuit breaker 25 A (B)	12
Surge capability (L/N-Ground)	2 kV
Surge capability (L-N)	1 kV
Nominal output voltage	24 V ²⁾
U-OUT (working voltage)	24.2 V
Nominal output power	160 W
Maximum output power	160 W ³⁾
Galvanic isolation	SELV
Galvanic isolation primary/secondary	3.75 kV
Input voltage DC	176...276 V
Output PWM frequency	> 2000 Hz
Output ripple Voltage (100 Hz)	< 1 %

¹⁾ at 230 V, 50 Hz

²⁾ DC voltage

³⁾ at steady state

Dimensions & weight



Mounting hole spacing, length	258.0 mm
Product weight	380.00 g
Cable cross-section, input side	0.5...2.5 mm ²
Cable cross-section, output side	0.5...2.5 mm ²
Wire preparation length, input side	6.0 mm
Wire preparation length, output side	6.0 mm
Length	300.0 mm
Width	50.0 mm
Height	35.0 mm

Colors & materials

Casing material	Plastic
-----------------	---------

Temperatures & operating conditions

Ambient temperature range	-20...+45 °C
Maximum temperature at tc test point	75 °C
Max.housing temperature in case of fault	110 °C
Temperature range at storage	-40...+85 °C
Permitted rel. humidity during operation	5...85 % ¹⁾

¹⁾ Maximum 56 days/year at 85 %

Lifespan

ECG lifetime	50000 h
--------------	---------

Additional product data

Predecessor EAN	4062172177948
-----------------	---------------

Capabilities

Dimmable	Yes
Dimming interface	DALI-2 / Corridor / Touch DIM
Dimming range	0.1...100 %
Dimming method	Pulse Width Modulation
Overheating protection	Automatic reversible
Overload protection	Automatic reversible
Short-circuit protection	Automatic reversible
No-load proof	Yes
Intended for no-load operation	No
Suitable for fixtures with prot. class	I / II
Type of connection, input side	Screw terminal
Type of connection, output side	Screw terminal
Control interface	DALI-2
Number of channels	1

Programming

Tuner4TRONIC	Yes
--------------	-----

Certificates & standards

Approval marks – approval	BIS / CCC / EAC / EL / ENEC 10 / RCM / VDE / VDE-EMC
Standards	Acc. to EN 55015/Acc. to EN 60598-2-22/Acc. to EN 61000-3-2/Acc. to EN 61347-1/Acc. to EN 61347-2-13/Acc. to EN 61547/Acc. to EN 62384/Acc. to EN 62386
Protection class	II
Type of protection	IP20

Logistical data

Commodity code	850440839000
----------------	--------------

Environmental information

Information according Art. 33 of EU Regulation (EC) 1907/2006 (REACH)	
Date of Declaration	23-06-2023
Primary Article Identifier	4062172274326
Candidate List Substance 1	Lead
CAS No. of substance 1	7439-92-1





Product datasheet

Safe Use Instruction	The identification of the Candidate List substance is sufficient to allow safe use of the article.
Declaration No. in SCIP database	67fd6178-7f13-4bfb-b80f-8f7a1fbc47d

Equipment / Accessories

- Suitable for 24 V LED modules

Download Data

File	
	User instruction OPTOTRONIC LED Power Supply
	Product Datasheet OTi DALI 160 220-240 24 2CH DT6-8 G3 Specification Sheet (EN)
	Product Datasheet OTi DALI 160 24 2CH DT6-8 G3 TDS 120522
	Certificates OT ENEC 40050684 041122

Ecodesign regulation information:

Intended for use with LED modules.

The forward voltage of the LED light source shall be within the defined operating window of the control gear in all operating conditions including dimming if applicable.

Separate control gear and light sources must be disposed of at certified disposal companies in accordance with Directive 2012/19/EU (WEEE) in the EU and with Waste Electrical and Electronic Equipment (WEEE) Regulations 2013 in the UK. For this purpose, collection points for recycling centres and take-back systems (CRSO) are available from retailers or private disposal companies, which accept separate control gear and light sources free of charge. In this way, raw materials are conserved and materials are recycled.

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4062172274326	OTi DALI 160/220-240/ 24 2CH DT6/8 G3	Shipping carton box 20	335 mm x 268 mm x 167 mm	14.99 dm ³	7918.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Product datasheet

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.