

Product Datasheet

Product code: **15AGHM.SA.0**

Product type: Cutting tweezers

Made in: Switzerland

Description: Type 15AGHM high precision cutting tweezers are suitable to applications which require cutting small material or performing small cuts. The extreme hard Tungsten Carbide blade insert is designed to cut the hardest metals.

Tip description: angled, cutting, superior finish

Tip material: K15

Coating/finishing: Sandblasted

Body material: Anti-Magnetic Anti-Acid Stainless Steel (SA)


Picture:



Tweezer dimensions:

OAL	115.0 mm – 4.528 inch
Width	10.0 mm – 0.394 inch
Height	16.0 mm – 0.630 inch

Tip details:



Tip dimensions:

Tip width	10.50 mm – 0.413 inch
Tip thickness	5.00 mm – 0.197 inch