

PRODUCT DATASHEET

HID LED HIGHBAY UNIVERSAL P 21000 LM 150W 840 E40

HID LED Highbay Universal P | LED replacement for HID lamps for high-bay luminaires



Areas of application

- LED alternative for applications requiring a high luminous flux
- Industrial and storage facilities
- Outdoor applications only in suitable luminaires

Product benefits

- Direct replacement for traditional HID lamps thanks to CCG and ignitor compatibility
- Operation on AC mains for highest energy efficiency possible
- Energy savings of up to 68 % when replacing traditional HQI lamps
- Effective thermal management for wide operating temperature range
- Low maintenance costs thanks to long lifetime
- Instant 100 % light, no warm-up time

Product features

- Type of protection: IP40
- High surge protection: up to 4 kV (L-N)



TECHNICAL DATA

Electrical data

Nominal wattage	150 W
Construction wattage	150.00 W
Nominal voltage	220...240 V
Claimed equiv. conventional lamp power	400 W
Nominal current	700 mA
Type of current	AC
Operating frequency	50/60 Hz
Mains frequency	50/60 Hz
Max. lamp no. on circuit break. 10 A (B)	8
Max. lamp no. on circuit break. B10 A - CCG without compensation	7
Max. lamp no. on circuit break. B10 A - CCG with compensation	6
Max. lamp no. on circuit break. 16 A (B)	15
Max. lamp no. on circuit break. B16 A - CCG without compensation	11
Max. lamp no. on circuit break. B16 A - CCG with compensation	10
Total harmonic distortion	20 %
Power factor λ	> 0.90

Photometrical data

Luminous intensity	9402 cd
Luminous flux	21000 lm
Nominal useful luminous flux 90°	21000 lm
Luminous efficacy	140 lm/W
Lumen main.fact.at end of nom.life time	0.70
Light color (designation)	Cool White
Color temperature	4000 K
Color rendering index Ra	80
Light color	840
Standard deviation of color matching	≤6 sdcn
Rated peak intensity	9402 cd
Flickering metric (Pst LM)	1
Stroboscope effect metric (SVM)	0,4



Light technical data

Beam angle	100 °
Warm-up time (60 %)	< 0.50 s
Starting time	< 0.5 s

Dimensions & Weight



Overall length	263.00 mm
Diameter	250.00 mm
Product weight	1380.00 g

Temperatures & operating conditions

Ambient temperature range	-40...+50 °C
Maximum temperature at tc test point	90 °C

Lifespan

Lifespan	50000 h ¹⁾
Number of switching cycles	100000
Lumen maintenance at end of service lifetime	0.70
Rated lamp survival factor at 6,000 h	≥ 0.90

¹⁾ L70/B50

Additional product data

Base (standard designation)	E40
-----------------------------	-----

Mercury content	0.0 mg
-----------------	--------

Capabilities

Dimmable	No
----------	----

Certificates & Standards

Energy efficiency class	D ¹⁾
Energy consumption	150.00 kWh/1000h
Type of protection	IP40
Standards	CE / EAC / UKCA
Photobiological safety group acc. to EN62778	RG1

¹⁾ Energy efficiency class (EEC) on a scale of A (highest efficiency) to G (lowest efficiency)

Country-specific categorizations

Order reference	HID LED HB UN P
-----------------	-----------------

LOGISTICAL DATA

Temperature range at storage	-40...+80 °C
------------------------------	--------------

Energy labelling regulation data acc EU 2019/2015

Lighting technology used	LED
Non-directional or directional	DLS
Mains or non-mains	MLS
Light source cap-type (or other electric interface)	E40
Connected light source (CLS)	No
Color-tuneable light source	No
Envelope	No
High luminance light source	No
Anti-glare shield	No
Correlated colour temperature type	SINGLE_VALUE
Standby power	0.00 W
Claim of equivalent power	No
Length	263.00 mm
Height	250.00 mm
Width	250.00 mm
Chromaticity coordinate x	0.382
Chromaticity coordinate y	0.38

R9 Colour rendering index	1
Beam angle correspondence	WIDE_CONE_120
Survival factor	0,90
Displacement factor	0.9
LED light source replaces a fluorescent light source	No
EPREL ID	1160650
Model number	AC41485









EQUIPMENT / ACCESSORIES


- Safety sling for lamp included

Safety advice

- The bulb may be larger and heavier than the replaced bulb. Before installation it must be checked, if the luminaire and especially the holder is capable of carrying the weight of the lamp. Safety sling has to be installed.
- To ensure full light efficiency and product lifetime, it is recommended to detach any glass or cover of the luminaire.
- Only suitable for temperatures of up to 50°C inside of the luminaire.
- Not suitable for operation with electronic control gear.

DOWNLOAD DATA

Documents and certificates	
	User instruction
	Declarations Of Conformity CE
	Declarations Of Conformity UKCA
Photometric and lighting design files	
	IES file (IES)
	LDT file (Eulumdat)
	UGR file (UGR table)
	LDC typ cone
	LDC typ polar

Photometric and lighting design files	
	Spectral power distribution

LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075780408	Folding box 1	255 mm x 255 mm x 320 mm	1700.00 g	20.81 dm³
4058075780415	Shipping box 4	530 mm x 530 mm x 348 mm	8474.00 g	97.75 dm³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.