

## Step Down 7 Click



PID: MIKROE-5754

**Step Down 7 Click** is a compact add-on board that converts higher voltages into a lower voltages level. This board features the [MAX17624](#), a synchronous step-down converter with integrated MOSFETs from [Analog Devices](#). The converter, as input, uses voltages in the range from 2.9V up to 5.5V and can output step-down voltages from 1.5V to 3.3V up to 1A. It features high efficiency, and depending on the mode of operation, it works at a fixed 4MHz switching frequency. In addition, it comes with undervoltage lockout, overcurrent protection, and thermal overload protection. This Click board™ makes the perfect solution for the development of power conversion solutions in automation and control applications, industrial sensors, test and measurement equipment, portable low-power devices, and more.

Step Down 7 Click is supported by a [mikroSDK](#) compliant library, which includes functions that simplify software development. This [Click board™](#) comes as a fully tested product, ready to be used on a system equipped with the [mikroBUS™](#) socket.

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.  
 ISO 14001: 2015 certification of environmental management system.  
 OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).

## Specifications

|                  |  |
|------------------|--|
| Type             | Buck   |
| Applications     | Can be used for the development of power conversion solutions in automation and control applications, industrial sensors, test and measurement equipment, portable low-power devices, and more   |
| On-board modules | MAX17624 - synchronous step-down converter with integrated MOSFETs from Analog Devices   |
| Key Features     | Internal soft start and pre-bias startup, overtemperature protection, overcurrent protection, 100% duty cycle operation, fixed 4MHz operation, PWM and PFM mode of operation, adjustable output, up to 1A of output current, digital potentiometer for feedback of the converter, and more |
| Interface        | GPIO,I2C   |
| ClickID          | Yes  |
| Compatibility    | mikroBUS   |
| Click board size | M (42.9 x 25.4 mm)   |
| Input Voltage    | 3.3V or 5V   |

## Resources

[mikroBUS™](#)

[mikroSDK](#)

[Click board™ Catalog](#)

[Click Boards™](#)

## Downloads

[Step Down 7 click example on Libstock](#)

[Step Down 7 click 2D and 3D files](#)

[Step Down 7 click schematic](#)

[MAX17624 datasheet](#)

[MCP4661 datasheet](#)

Mikroe produces entire development toolchains for all major microcontroller architectures.

Committed to excellency, we are dedicated to helping engineers bring the project development up to speed and achieve outstanding results.



ISO 27001: 2013 certification of informational security management system.  
 ISO 14001: 2015 certification of environmental management system.  
 OHSAS 18001: 2008 certification of occupational health and safety management system.



ISO 9001: 2015 certification of quality management system (QMS).