




Part Number : [1205000340](#)
Product Description : Micro-Change (M12)
Single-Ended Cordset, 4 Poles, L-Coded,
Female (90°) to Pigtail, 16 AWG, Black TPU
WSOR Cable, 15.0m (49.21') Length
Series Number : 120500
Status : Active
Product Category : Circular Industrial
Cordsets
Engineering Number : L0P4001B43M150



Documents & Resources

Drawings
[Drawing 1205000340_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120500
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, L-Coded, Female (90°) to Pigtail, 16 AWG, Black TPU WSOR Cable, 15.0m (49.21') Length
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Region	Asia, Europe
Type	Single Ended
UPC	196823150647

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	63V

Physical

Cable Diameter	7.90mm (.311")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail

Keyway	L-Coded
LED Indicator	No
Material - Cable Jacket	WSOR TPU
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	FKM
Material - Plating Mating	Gold
Net Weight	1514.938/g
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	16