

TECHNICAL DATA SHEET

PRO-ELEC

**RoHS
Compliant**

REWIREABLE PLUG-IN RCD

MODEL: PEL00415A

FEATURES

RCD plug is made of ASIC and special material with high susceptibility and reliability.

When appliance leakage happens or user gets an electric shock, plug can automatically cut off power promptly, protecting appliance and user's life.

Has waterproof and dustproof functions, with reliable fuse and wears well.

Users can assemble cable by themselves.

It is applicable to leakage protection of overseas hand-held electric tool, electric pump, high pressure electric cleaner, electric grass cutter, electric water heater, strong release gas water heater, solar energy water heater, electric water boiler, air-conditioner, rice cooker, induction cooker, computer, TV set, refrigerator, washing machine, hair dryer, electric iron, etc.



SPECIFICATIONS

Rated Voltage: 250V AC, 50Hz

Rated Current: 13A

Max. Power: 3,250W

Rated Leakage Tripping Current: 30mA

Rated Leakage No Tripping Current: 15mA

Max. Tripping Time: $\leq 0.3s$

Polarity Number (Pole): Line, Zero, Ground

Operating Temperature: $-5^{\circ}C$ to $+40^{\circ}C$

Protection Class: IP54

Air Relative Degree of Humidity: $\leq 93\%$ ($25^{\circ}C$)

Important Notice: This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC

TECHNICAL DATA SHEET

PRO-ELEC

RoHS
Compliant

ATTENTION

Only for indoor use.

Make sure the TEST button can be tripped before use, otherwise do not use the device.

The TEST and RESET buttons can't be use as "on-off" switch for line.

Important Notice: This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

PRO-ELEC