

# Numatic Product Information Sheet

## VNP180



Rated Motor Power (W)	620 W
Power	230v AC 50/60Hz
Airflow Motor only	48 L/sec
Max Suction H <sub>2</sub> O	2300
Kit	NA1
Capacity	6 Litres
Cleaning Range	26.4 m
Weight (Ready to use)	6.0 kg
Dimensions (W x L x H)	340mm x 365mm x 360mm
Mains Lead	HO5-V2V2-F 10.0 x 2 x 1.00 mm <sup>2</sup>
Protection Class	Class II
Sound Pressure	LpA ≤ 70 dB(A)
Filter Type	TriTex
Dust Bag	NVM 1CH

NuVac

Designed to work for a living and work hard.

**High Efficiency Motor**

**10.0 Metre Cable**

**TriTex Filtration System**

**Wand Docking**

**HepaFlo Bags**

**Professional Accessory Set**

UNITED KINGDOM: [www.numatic.co.uk](http://www.numatic.co.uk)

NETHERLANDS: [www.numatic.nl](http://www.numatic.nl)

PORTUGAL: [www.numatic.pt](http://www.numatic.pt)

GERMANY: [www.numatic.de](http://www.numatic.de)

SWITZERLAND: [www.numatic.ch](http://www.numatic.ch)

SPAIN: [www.numatic.es](http://www.numatic.es)

FRANCE: [www.numatic.fr](http://www.numatic.fr)

SOUTH AFRICA: [www.numatic.co.za](http://www.numatic.co.za)

*Specification subject to change without prior notice*  
[www.numatic.co.uk](http://www.numatic.co.uk) © Numatic International Limited