

PRODUCT DATASHEET FL PFM ASYM 45x140 150 W 4000 K BK

FLOODLIGHT PERFORMANCE ASYM 45x140 | Floodlight with very wide beam, asymmetric light distribution for area lighting



Areas of application

- Direct replacement for luminaires using HID lamps
- Outdoor use (IP66)
- Parking
- Public areas
- Industry
- Sports facilities
- Parking lots, industrial roads
- D-sign according to EN 60598-2-24 for fire-risk commercial unit, e.g. by accumulation of dust

Product benefits

- Energy savings of up to 90 % compared to halogen lamp floodlights
- Energy savings of up to 45 % compared to luminaires that use conventional discharge lamps
- Bright, robust and durable
- Homogeneous luminance distribution and reduced glare
- No upper light output ratio (ULOR 0%) when mounted at 0° tilt
- Key hole to ensure ease of installation
- 5 years guarantee

Product features

- High luminous efficacy: up to 140 lm/W
- Asymmetric light distribution for area lighting
- Angled (45°) mounting bracket and up to 180° tilting
- Type of protection: IP66
- Impact resistance: IK08



- Ambient temperature in operation: -30...+50 °C
- High surge protection: up to 10 kV (L/N-PE), 6 kV (L-N)
- Integrated breather for preventing condensation inside the luminaire
- Connection via 2 m cable, wiring required


TECHNICAL DATA

Electrical data


Nominal wattage	150.00 W
Nominal voltage	220240 V
Mains frequency	5060 Hz
Nominal current	735 mA
Inrush current	110 A
Inrush current time T _{h50}	200 μs
Max. no. of lum. on circuit break. B16 A	3
Max. no. of lum. on circuit break. C10 A	2
Max. no. of lum. on circuit break. C16 A	4
Power factor λ	> 0.90
Total harmonic distortion	< 20 %
Protection class	1
Operating mode	Integrated LED driver

Photometrical data

Luminous flux	19800 lm	
Luminous efficacy	130 lm/W	
Color temperature	4000 K	
Light color (designation)	Cool White	
Color rendering index Ra	> 80	
Standard deviation of color matching	≤5 sdcm	
Luminous intensity	-	
Low flicker	Yes	
Flickering metric (Pst LM)	-	
Stroboscope effect metric (SVM)	-	
Photobiological safety group acc. to EN62778	RG1	
Beam angle	45 ° x 140 °	







Dimensions & Weight

Length	451.00 mm
Width	330.00 mm
Height	77.00 mm
Product weight	4500.00 g
Cable length	2000 mm



Materials & Colors

Product color	Black
Housing color	Black
Body material	Aluminum
Cover material	Glass
Light emitting surface material	Glass
Glow Wire Test according to IEC 60695-2-12	650 °C
Mercury content	0.0 mg

Application & Mounting

And the table of the same and t	70 50.05
Ambient temperature range	-30+50 °C
Temperature range at storage	-40+70 °C
Type of connection	Cable, 3-pole
Type of protection	IP66
Protection class IK (shock resistance)	IK08
Dimmable	No
Mounting type	Surface
Mounting location	Wall / Pole / Floor / Ceiling
Application environment	Outdoor
Adjustable	Yes
LED module replaceable	Not replaceable
With light source	Yes

Lifespan

Lifespan L70/B50 at 25 °C	100000 h ¹⁾
Lifespan L80/B10 at 25 °C	70000 h ¹⁾
Lifespan L90/B10 at 25 °C	30000 h
Number of switching cycles	100000

¹⁾ _t[h]: L70 / B50 @ 25 °C (Ta), t[h]: L80 / B10 @ 25 °C (Ta), t[h]: L90 / B10 @ 25 °C (Ta)

Control gear

Output current	2900 mA
ECG - Output ripple current	< 10 %

Certificates & Standards

Standards	CE / CB / ENEC / TÜV SÜD / EAC
Luminaire with limited surface temperature, "D sign"	Yes
Ball shot safe	No

DOWNLOAD DATA

	Documents and certificates
PDF	User instruction
PDF	Addon Technical Information


	Documents and certificates
POF	Packaging insert
POF	Declarations Of Conformity CE
POF	Declarations Of Conformity UKCA
	Photometric and lighting design files
	IES file (IES)
	LDT file (Eulumdat)
	ULD file (DIALux)
	ROLF file (RELUX)
	LDC typ polar
	CAD/BIM files
ZIP	BIM_Revit_3D
	CAD_STEP_3D
	Tender texts
	Tender documents


LOGISTICAL DATA


Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075353701	Shipping box 1	516 mm x 130 mm x 368 mm	4970.00 g	24.69 dm ³

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

ADDITIONAL CATALOG INFORMATION







References / Links

- For Guarantee see www.ledvance.com/guarantee

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.