

# PRODUCT DATASHEET

## SPYLUX White

SPYLUX® | Little helpers



---

### Product benefits

- Can be removed from the holder for use as a portable light

---

### Product features

- Battery operated dustproof and splashproof luminaire
- Rotating head for versatile use
- Integrated motion sensor



## TECHNICAL DATA

### Electrical data


Nominal wattage	0.3W
Nominal voltage	4,5 V
Mains frequency	0 Hz
Nominal current	60.000 mA
Max. no. of lum. on circuit break. B16 A	-
Max. no. of lum. on circuit break. C10 A	-
Max. no. of lum. on circuit break. C16 A	-
Protection class	III
Operating mode	Battery

### Photometrical data

Luminous flux	17 lm
Luminous efficacy	57 lm/W
Color temperature	3000 K
Light color (designation)	Warm White
Color rendering index Ra	> 85
Standard deviation of color matching	≤6 sdcn
Beam angle	115 °

### Dimensions & Weight

Length	68.00 mm
Width	68.00 mm
Height	99.00 mm
Product weight	105.00 g



### Materials & Colors

Product color	White
Housing color	White
Body material	Polycarbonate (PC)
Mercury content	0.0 mg

### Application & Mounting

Ambient temperature range	-20...+30 °C
Temperature range at storage	-20...+60 °C
Type of protection	IP43
Dimmable	No
Mounting type	Surface
Mounting location	Wall
Application environment	Indoor
Adjustable	Yes
LED module replaceable	Not replaceable
With light source	Yes

### Lifespan

Lifespan L70/B50 at 25 °C	10000 h <sup>1)</sup>
Number of switching cycles	15000

<sup>1)</sup> t[h]: L70 / B50 @ 25 °C (Ta), t[h]: L80 / B10 @ 25 °C (Ta), t[h]: L90 / B10 @ 25 °C (Ta)

### Sensor

Type of sensor	Motion
Sensor technology	Passive infrared (PIR)

### Emergency lighting

Nominal voltage of battery	1.5 V
----------------------------	-------

### Certificates & Standards

Standards	CE / UKCA
-----------	-----------

### EQUIPMENT / ACCESSORIES

– Can be mounted with screws, adhesive strip or magnet

### DOWNLOAD DATA

## Documents and certificates



Declarations Of Conformity CE

## LOGISTICAL DATA

Product code	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Gross weight	Volume
4058075227835	Blister 1	68 mm x 140 mm x 195 mm	125.00 g	1.86 dm <sup>3</sup>
4058075227842	Shipping box 6	421 mm x 154 mm x 210 mm	941.00 g	13.62 dm <sup>3</sup>

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

## DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.