

https://www.phoenixcontact.com/in/products/1050771

**PHŒNIX** CONTACT

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Photovoltaic connector, Range of articles: Sunclix, housing material: PPE, color: black, number of positions: 1, min. conductor cross section: 2.5 mm<sup>2</sup>, max. conductor cross section: 6 mm<sup>2</sup>, rated voltage: 1500 V DC, rated current: 40 A, Connection method: Crimp, Contact connection type: Socket, min. cable diameter: 5 mm, max. cable diameter: 8 mm

### Your advantages

- · Crimp connection technology for automated assembly processes
- · High yield, thanks to silver-plated contacts
- · International approvals in accordance with IEC and UL enable worldwide use
- Unique SUNCLIX pin connector pattern

#### Commercial data

Item number	1050771	
Packing unit	50 pc	
Minimum order quantity	50 pc	
Sales key	ABL	
Product key	ABLBBB	
GTIN	4055626669632	
Weight per piece (including packing)	10.5 g	
Weight per piece (excluding packing)	9.821 g	
Customs tariff number	39269097	
Country of origin	IN	

1050771

https://www.phoenixcontact.com/in/products/1050771

## **DPHŒNIX** CONTACT

### Technical data

#### Notes

afety note	
Safety note	WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.
	<ul> <li>WARNING: Only electrically qualified personnel may install an operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.</li> </ul>
	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.
	<ul> <li>The products are suitable for applications in plant, controller, and electrical device engineering.</li> </ul>
	<ul> <li>Assembled products may not be manipulated or improperly opened.</li> </ul>
	<ul> <li>Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products).</li> </ul>
	<ul> <li>When using the product in direct connection with third-party manufacturers, the user is responsible.</li> </ul>
	<ul> <li>For operating voltages &gt; 50 V AC, conductive connector housings must be grounded</li> </ul>
	<ul> <li>Ensure that the protective or functional ground has been properly connected.</li> </ul>
	<ul> <li>Observe the corresponding technical data. You will find information:</li> <li>O n the product</li> <li>O n the packing label</li> <li>In the supplied documentation</li> <li>O nline at phoenixcontact.com/products under the product</li> </ul>
	<ul> <li>The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product.</li> </ul>
	<ul> <li>Use a protective cap to protect connectors that are not in use.</li> <li>The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products</li> </ul>
	<ul> <li>The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12).</li> </ul>
	<ul> <li>Operate the connector only when it is fully plugged in and interlocked.</li> </ul>
	<ul> <li>Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.</li> </ul>



#### 1050771

https://www.phoenixcontact.com/in/products/1050771

• Observe the minimum bending radius of the cable. Lay the	
cable without twisting it.	

#### Product properties

Product type	Photovoltaic connector	
Product family	Sunclix	
Number of positions	1	
Insulation characteristics		

П

2

### Protection class

FIDIECTION	1055
Degree of p	ollution

Electrical properties	
Rated voltage (II/2)	1500 V
Nominal voltage ATD	1500 V DC (II/2) in accordance with IEC 62852:2014/AMD1:2020
	1500 V DC in accordance with UL 6703
Rated surge voltage	16 kV
Rated surge voltage (III/3)	16 kV
Rated current	40 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current (4.0 mm <sup>2</sup> )	34 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current (2.5 mm <sup>2</sup> )	27 A (in accordance with IEC 62852:2014/AMD1:2020)
Rated current	50 A (in accordance with UL 6703)
	35 A (in accordance with UL 6703)
	30 A (in accordance with UL 6703)
Contact resistance	≤ 0.45 mΩ
Contact resistance	< 0.3 m $\Omega$ (Crimp to crimp)

#### Dimensions

Width	20 mm
Height	20 mm
Length	72.8 mm

#### Material specifications

Color	black
Color of the housing part	black
Flammability rating according to UL 94	V0
Insulating material group	II
Insulating material	mPPE
Cable seal material	EPDM
Contact material	Cu
Contact surface material	Ag
O-ring material	Silopren LSR 2660
Housing material	PPE

Cable/line



#### 1050771

https://www.phoenixcontact.com/in/products/1050771

Oshla Las		
Cable type		H1Z2Z2-K lines
External cable diameter ()		5 mm 8 mm
External cable diameter		5 mm 8 mm
Single wire, cross section		2.5 mm <sup>2</sup> 6 mm <sup>2</sup> 14 AWG 10 AWG
Stripping length of the indivi	dual wire	9 mm -1 mm
Cable pull-out force		> 80 N (IEC 62852:2014)
Mechanical properties		
Outside conductor diameter		5 mm 8 mm
Mechanical data		
Outside conductor diameter		5 mm 8 mm
Insertion/withdrawal cycles		100
Insertion force Withdrawal force		45 N ±10 N
		250 N ±50 N (when locked)
Environmental and real-life	conditions	
Ambient conditions	conditions	IP66 / IP68 (2 m / 24 h) (plugged in)
	conditions	IP66 / IP68 (2 m / 24 h) (plugged in) IP20 (Not plugged in)
Ambient conditions	conditions	IP66 / IP68 (2 m / 24 h) (plugged in) IP20 (Not plugged in) IP66 / IP68 (2 m / 24 h)
Ambient conditions		IP20 (Not plugged in)
Ambient conditions Degree of protection	ation)	IP20 (Not plugged in) IP66 / IP68 (2 m / 24 h)
Ambient conditions Degree of protection Ambient temperature (operation)	ation) mbly)	IP20 (Not plugged in) IP66 / IP68 (2 m / 24 h) -40 °C 85 °C (dependent on the derating curve)

#### Mounting

Connection method	Crimp
-------------------	-------



1050771

https://www.phoenixcontact.com/in/products/1050771

#### Approvals

🌣 To download certificates, visit the product detail page: https://www.phoenixcontact.com/in/products/1050771

<b>F</b>	UL Recognized Approval ID: E477377-2	0230908			
		Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
		1500 V	50 A	14 - 10	-



TÜV Rheinland Approval ID: R 60159495-0001



1050771

https://www.phoenixcontact.com/in/products/1050771

## Classifications

#### ECLASS

ECLASS-11.0	27440107
ECLASS-12.0	27440107
ECLASS-13.0	27440107

#### ETIM

	ETIM 9.0	EC002635	
UNSPSC			
	UNSPSC 21.0	39121400	



1050771

https://www.phoenixcontact.com/in/products/1050771

### **PHŒNIX** CONTACT

## Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

1050771

https://www.phoenixcontact.com/in/products/1050771



Accessories

PV-C PROTECTION CAP - Protective cap

1785430 https://www.phoenixcontact.com/in/products/1785430

Protective cap, Range of articles: Sunclix, color: black. self-sealing, without interlock, set consisting of: 1 protective cap for connector side and 1 protective cap for coupling side



#### PV-C3F-C-6-R3000 - Crimp contact

1050767 https://www.phoenixcontact.com/in/products/1050767



Crimp contact, Range of articles: Sunclix, color: silver, number of positions: 1, min. conductor cross section: 6 mm<sup>2</sup>, max. conductor cross section: 6 mm<sup>2</sup>, rated current: 40 A, Connection method: Crimp, Contact connection type: Socket. Crimping recommendation: Crimp the conductor with the crimp contact in accordance with IEC 60352

1050771

https://www.phoenixcontact.com/in/products/1050771



PV-C3F-C-2,5-4-R3000 - Crimp contact

1050769

https://www.phoenixcontact.com/in/products/1050769



Crimp contact, Range of articles: Sunclix, color: silver, number of positions: 1, min. conductor cross section:  $2.5 \text{ mm}^2$ , max. conductor cross section:  $4 \text{ mm}^2$ , rated current: 27 A, Connection method: Crimp, Contact connection type: Socket. Crimping recommendation: Crimp the conductor with the crimp contact in accordance with IEC 60352

#### CRIMPFOX-P SR 6 - Crimping pliers

1212755 https://www.phoenixcontact.com/in/products/1212755



Crimping pliers, for SUNCLIX solar crimp connectors 2.5 ... 6 mm<sup>2</sup>, unlockable pressure lock, precise parallel crimping, lateral entry, B crimp, incl. positioning tool

1050771

https://www.phoenixcontact.com/in/products/1050771



PV-A-C-DC-TOOL - Contact removal tool

1069522 https://www.phoenixcontact.com/in/products/1069522

Contact removal tool, Range of articles: Sunclix



Phoenix Contact 2023 © - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT (I) Pvt. Ltd. A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420 info@phoenixcontact.co.in