

IEC Type J PTFE Insulated Twin Twisted Pair Thermocouple Cable / Wire



Labfacility are the UK's leading manufacturer of Temperature Sensors, Thermocouple Connectors and associated Temperature Instrumentation and stockists of Thermocouple Cables. The Company has been trading since 1971 and is ISO 9001 accredited.

Labfacility have supplied Farnell for over 30 years, and an extensive range of our products are available to buy online, from stock, direct from Farnell.

Datasheet



Specifications

General Description Resistant to oils, acids adverse agents and fluids.					
	Good mechanical strength and flexibility.				
Cable Length	10m, 25m, 50m, 100m				
Cable Type	Twin twisted pair for extending or making simple				
	thermocouples				
Core / Strands	1/0.2mm , 7/0.2mm, 1/0.315mm, 1/0.508mm				
Conductor Cross Section 1/0.2 (mm2)	0.032				
Conductor Cross Section 1/0.315 (mm2)	0.078				
Conductor Cross Section 1/0.508 (mm2)	0.203				
Conductor Cross Section 7/0.2 (mm2)	0.219				
+ Colour	Black				
- Colour	White				
Drain Wire	No				
Insulation Material	PTFE insulated				
Loop Resistance 1/0.2	19.3				
(Ohms per combined metre)					
Loop Resistance 1/0.315	7.8				
(Ohms per combined metre)					
Loop Resistance 1/0.508	3.0				
(Ohms per combined metre)					
Loop Resistance 7/0.2	2.7				
(Ohms per combined metre)					
Max. Temperature	+260°C				
Min. Temperature	-75°C				
+ Conductor	Iron				
- Conductor	Constantan				
Screen	No				
Standards Met	Colour code (cores & jacket) to IEC-584-3				
Thermocouple Type	J				
Tolerance	Class 1				

Datasheet

Ordering Information

ABFAC

TEMPERATURE & PROCESS TECHNOLOGY

Туре	Colour Code	Cable Style	Strand Size	Length	Manufacturers Code	Farnell Order Code
J	IEC	PTFE TWIN TWISTED	1/0.2mm	25m (82ft)	WJ-244-D	3358150
J	IEC	PTFE TWIN TWISTED	1/0.2mm	50m (164.1ft)	WJ-244-D	2918707
J	IEC	PTFE TWIN TWISTED	1/0.2mm	100m (328.1ft)	WJ-244-D	4073318
J	IEC	PTFE TWIN TWISTED	1/0.315mm	10m (32.8ft)	WJ-245-D	3582289
J	IEC	PTFE TWIN TWISTED	1/0.315mm	25m (82ft)	WJ-245-D	3582290
J	IEC	PTFE TWIN TWISTED	1/0.315mm	50m (164.1ft)	WJ-245-D	3582291
J	IEC	PTFE TWIN TWISTED	1/0.315mm	100m (328.1ft)	WJ-245-D	3582292
J	IEC	PTFE TWIN TWISTED	1/0.508mm	10m (32.8ft)	WJ-246-D	3582296
J	IEC	PTFE TWIN TWISTED	1/0.508mm	25m (82ft)	WJ-246-D	3582293
J	IEC	PTFE TWIN TWISTED	1/0.508mm	50m (164.1ft)	WJ-246-D	3582294
J	IEC	PTFE TWIN TWISTED	1/0.508mm	100m (328.1ft)	WJ-246-D	3582295
J	IEC	PTFE TWIN TWISTED	7/0.2mm	10m (32.8ft)	WJ-243-D	3582285
J	IEC	PTFE TWIN TWISTED	7/0.2mm	25m (82ft)	WJ-243-D	3582286
J	IEC	PTFE TWIN TWISTED	7/0.2mm	50m (164.1ft)	WJ-243-D	3582287
J	IEC	PTFE TWIN TWISTED	7/0.2mm	100m (328.1ft)	WJ-243-D	3582288

