

Product datasheet

Specifications



Lexium 62 Double Drive 27 A - accessory kit included

LXM62DD27D21000

Main

Range Of Product	PacDrive 3
Product Or Component Type	Double drive
Device Short Name	LXM 62

Complementary

Product Compatibility	Servo motor SHS Servo motor SH3 (100 mm, 3 motor stacks) optimized in terms of torque and speed Servo motor SH3 (100 mm, 4 motor stacks) optimized in terms of torque and speed Servo motor SH3 (140 mm, 1 motor stacks) optimized in terms of torque and speed Servo motor MH3 (100 mm, 2 motor stacks) optimized in terms of torque and speed
Network Number Of Phases	Three phase
[Us] Rated Supply Voltage (Through Power Supply Module)	400 V (- 10...10 %) for three phase 230 V (- 10...10 %) for three phase 230 V (- 10...10 %) for single phase
Supply Frequency	50/60 Hz - 5...5 %
Continuous Output Current	9 A at 4 kHz
Output Current 3S Peak	27 A at 4 kHz
Continuous Power	4.3 kW
Nominal Power	4.3 kW
Switching Frequency	8 kHz
Overvoltage Category	III
Electrical Connection	Terminal, clamping capacity: 0.2...15 mm ² , AWG 24...AWG 16 (CN4) Terminal, clamping capacity: 0.5...16 mm ² , AWG 20...AWG 6 (CN5) Terminal, clamping capacity: 0.75...16 mm ² , AWG 18...AWG 6 (CN6) Terminal, clamping capacity: 0.2...6 mm ² , AWG 24...AWG 10 (CN7)
Tightening Torque	CN1: 2.5 N.m
Number Of Inputs	2 digital 2 touch probe
Discrete Input Voltage	24 V DC for - 20...25 %
Number Of Outputs	2 digital
Discrete Output Voltage	24 V DC
Safety Function	STO (safe torque off)
Communication Interface	SERCOS III, integrated
Depth	270 mm
Height	310 mm
Width	44.5 mm

Net Weight	3 kg
------------	------

Environment

Standards	IEC 62061 IEC 61800-5-1 IEC 61800-3 CSA C22.2 No 14 IEC 61508 UL 508C ISO 13849-1 IEC 61800-5-2 ISO 13849-2 IEC 62061
-----------	--

Product Certifications	CE EAC TÜV CSA UL
------------------------	-------------------------------

Ip Degree Of Protection	IP20 conforming to IEC 60529
-------------------------	------------------------------

Vibration Resistance	10 m/s ² conforming to IEC 60721-3-3
----------------------	---

Shock Resistance	100 m/s ² conforming to IEC 60721-3-3
------------------	--

Pollution Degree	2 conforming to IEC 61800-5-2
------------------	-------------------------------

Environmental Characteristic	3K3 conforming to IEC 60721-3-3
------------------------------	---------------------------------

Relative Humidity	5...85 %
-------------------	----------

Ambient Air Temperature For Operation	5...55 °C
---------------------------------------	-----------

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
------------------------------	---

Package 1 Height	10.600 cm
------------------	-----------

Package 1 Width	33.000 cm
-----------------	-----------

Package 1 Length	44.000 cm
------------------	-----------

Package 1 Weight	3.994 kg
------------------	----------

Unit Type Of Package 2	P06
------------------------	-----

Number Of Units In Package 2	10
------------------------------	----

Package 2 Height	75.000 cm
------------------	-----------

Package 2 Width	60.000 cm
-----------------	-----------

Package 2 Length	80.000 cm
------------------	-----------

Package 2 Weight	49.940 kg
------------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Pvc Free

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)