

200mm 550W 230V HEAVY DUTY BENCH GRINDER

CATALOGUE ENTRY

58 GHD200
200mm 550W 230V HEAVY DUTY
BENCH GRINDER

A heavy duty model designed for use in the garage or industrial workshop. One coarse and one fine grinding wheel, adjustable eye protection shields, spark deflectors, wheel guards and tool rests. An integral cooling trough is included in the base of the machine. Fitted with a BS approved non-rewireable 3 pin moulded plug and cable. Display carton.

Specification:

Grinding wheel diameter	... 200mm
Bore size	... 16mm
Speed	... 3000rpm
Machine dimensions	... 400 x 245 x 270mm
Weight	... 21kg

Stock No.	Euro each	GBP £ each
29621	N/a	N/a

DRAPER BULLETS

these need to be kept to a minimum, in order of priority.

- 3000rpm
- one fine and one coarse grinding wheel
- Industrial machine



Stock No.	Chk Digit	Description	FARNELL CODE
29621	7	230V 200MM HEAVY DUTY BENCH GRINDER	3226130

BRAND:	DRAPER	BARCODED	YES
--------	---------------	----------	------------