## **110V 2FT**ANTI-CORROSIVE FITTING













#### **FEATURES:**

- IP65 Weather Proof
- 4ft and 5ft sizes are also available
- Available with a Tripod (232148) and a Plasterer's A-Frame (232131)
- High Quality
- Robust and Durable product

#### **APPLICATIONS**







OUTDOOR

**20W** 

# **110V 2FT**ANTI-CORROSIVE FITTING

Part No.	232094
DESCRIPTION	110V 2ft Anti-Corrosive Fitting
DIMENSIONS	640mm x 82mm x 72mm
BODY COLOUR	Yellow
POWER CONSUMPTION	20W
POWER INPUT	100-120V
COLOUR TEMPERATURE	4000K
COLOUR RENDITION (CRI)	Ra >80
LUMEN OUTPUT/MODES	2200lm
IP RATING	IP65
IK RATING	IK10
BEAM ANGLE	120°
CONSTRUCTION	Polycarbonate
WORKING TEMPERATURE	-20°C to +45°C
LIFETIME (HRS)	50,000
SWITCH CYCLES	15,000
CERTIFICATION	UKCA, CE
WARRANTY	1 year (+ 4 year extended warranty with online registration)
EFFICACY RATING	110lm/W

### **ADDITIONAL ACCESSORIES**

Part No.	232148
DESCRIPTION	2ft Anti-Corrosive with Tripod Available
DIMENSIONS	260mm



Part No.	232131
DESCRIPTION	2ft Anti-Corrosive with Plasterer's A-Frame Available
DIMENSIONS	270mm x 310mm x 950mm







**BRIGHT SOURCE** 

232094





**20** kWh/1000h

