



SAFETY DATA SHEET

PDF1 / DDF1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name DDF1 Detectadusta / PDF1 Pressuredusta

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Air Duster

1.3. Details of the supplier of the safety data sheet

Supplier Gas Safe Europe Ltd
Chowley One, Chowley Oak Lane
Tattenhall, Chester CH3 9GA
Great Britain+44(0)1352 860600
enquiries@gassafeurope.com

1.4. Emergency telephone number

Emergency telephone +44 (0) 1352860600 (MON TO FRI 09:00 - 17:00)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Aerosol 1 - H222, H229

Health hazards Not Classified

Environmental hazards Not Classified

Human health Vapours and spray/mists in high concentrations are narcotic. See Section 11 for additional information on health hazards.

Environmental The product is not expected to be hazardous to the environment.

Physicochemical Containers can burst violently or explode when heated, due to excessive pressure build-up. The product is extremely flammable. Vapours may form explosive mixtures with air.

2.2. Label elements

Hazard pictograms



Signal word Danger

PDF1 / DDF1

Hazard statements	H222 Extremely flammable aerosol. H229 Pressurised container: may burst if heated.
Precautionary statements	P102 Keep out of reach of children. P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 Do not spray on an open flame or other ignition source. P251 Do not pierce or burn, even after use. P261 Avoid breathing vapour/ spray. P271 Use only outdoors or in a well-ventilated area. P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients**3.2. Mixtures**

PETROLEUM GASES, LIQUEFIED <0.1% 1,3-BUTADIENE	60-100%
CAS number: 68476-85-7	EC number: 270-704-2
Classification Flam. Gas 1 - H220 Press. Gas (Comp.) - H280	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures**4.1. Description of first aid measures**

General information	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Get medical attention if any discomfort continues.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. If in doubt, get medical attention promptly.
Ingestion	No specific recommendations.
Skin contact	Get medical attention promptly if symptoms occur after washing.
Eye contact	Remove any contact lenses and open eyelids wide apart. Rinse immediately with plenty of water. Continue to rinse for at least 15 minutes. Get medical attention promptly if symptoms occur after washing.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

4.2. Most important symptoms and effects, both acute and delayed

General information	See Section 11 for additional information on health hazards.
----------------------------	--

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

SECTION 5: Firefighting measures**5.1. Extinguishing media**

Suitable extinguishing media	Carbon dioxide or dry powder.
-------------------------------------	-------------------------------

5.2. Special hazards arising from the substance or mixture

PDF1 / DDF1

Specific hazards Containers can burst violently or explode when heated, due to excessive pressure build-up.

5.3. Advice for firefighters

Protective actions during firefighting Use water to keep fire exposed containers cool and disperse vapours. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid inhalation of vapours and contact with skin and eyes. Ensure suitable respiratory protection is worn during removal of spillages in confined areas.

6.2. Environmental precautions

Environmental precautions No specific requirements are anticipated under normal conditions of use.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Eliminate all sources of ignition. No smoking, sparks, flames or other sources of ignition near spillage. Provide adequate ventilation.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Keep away from heat, sparks and open flame. Read and follow manufacturer's recommendations. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited. Use suitable respiratory protection if ventilation is inadequate.

Advice on general occupational hygiene Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Protect from freezing and direct sunlight. Store in a dry place. Do not store near heat sources or expose to high temperatures. Keep away from heat, sparks and open flame.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

PETROLEUM GASES, LIQUEFIED <0.1% 1,3-BUTADIENE

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1750 mg/m³

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1750 mg/m³

Short-term exposure limit (15-minute): WEL 1250 ppm 2180 mg/m³

Short-term exposure limit (15-minute): WEL 1250 ppm 2180 mg/m³

WEL = Workplace Exposure Limit

8.2. Exposure controls

Eye/face protection Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

PDF1 / DDF1

Hand protection	No specific requirements are anticipated under normal conditions of use.
Other skin and body protection	Wear suitable protective equipment for prolonged exposure and/or high concentrations of vapours, spray or mist.
Respiratory protection	No specific recommendations. If ventilation is inadequate, suitable respiratory protection must be worn.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	Aerosol.
Colour	Colourless.
Odour	No characteristic odour.
Odour threshold	No information available.
pH	No information available.
Melting point	No information available.
Initial boiling point and range	-41°C
Flash point	-40°C Closed cup.
Evaporation rate	No information available.
Evaporation factor	No information available.
Flammability (solid, gas)	No information available.
Upper/lower flammability or explosive limits	Lower flammable/explosive limit: 1.8 % Upper flammable/explosive limit: 9.5 %
Vapour pressure	No information available.
Vapour density	No information available.
Relative density	0.535
Solubility(ies)	Immiscible with water.
Partition coefficient	No information available.
Auto-ignition temperature	495°C
Decomposition Temperature	No information available.
Viscosity	No information available.
Explosive properties	No information available.
Oxidising properties	No information available.

9.2. Other information

Other information	None.
--------------------------	-------

SECTION 10: Stability and reactivity**10.1. Reactivity**

Reactivity	No test data specifically related to reactivity available for this product or its ingredients.
-------------------	--

10.2. Chemical stability

Stability	Stable at normal ambient temperatures and when used as recommended.
------------------	---

PDF1 / DDF1**10.3. Possibility of hazardous reactions**

Possibility of hazardous reactions None known.

10.4. Conditions to avoid

Conditions to avoid Avoid heat, flames and other sources of ignition. Avoid exposing aerosol containers to high temperatures or direct sunlight.

10.5. Incompatible materials

Materials to avoid None known.

10.6. Hazardous decomposition products

Hazardous decomposition products None at ambient temperatures.

SECTION 11: Toxicological information**11.1. Information on toxicological effects**

Inhalation Vapours in high concentrations are narcotic. Vapours may cause headache, fatigue, dizziness and nausea.

Skin contact Skin irritation should not occur when used as recommended.

Eye contact Vapour or spray in the eyes may cause irritation and smarting.

Acute and chronic health hazards No known chronic or acute health risks.

Route of exposure Inhalation Skin and/or eye contact

SECTION 12: Ecological information**12.1. Toxicity****12.2. Persistence and degradability**

Persistence and degradability No data available.

12.3. Bioaccumulative potential

Partition coefficient No information available.

12.4. Mobility in soil

Mobility No data available.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment This product does not contain any substances classified as PBT or vPvB.

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

General information Dispose of waste product or used containers in accordance with local regulations Waste codes should be assigned by the user, preferably in discussion with the waste disposal authorities.

PDF1 / DDF1

Disposal methods	Containers should be thoroughly emptied before disposal because of the risk of an explosion. Do not pierce or burn, even after use.
Waste class	The waste code classification is to be carried out according to the European Waste Catalogue (EWC).

SECTION 14: Transport information**14.1. UN number**

UN No. (ADR/RID)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950
UN No. (ADN)	1950

14.2. UN proper shipping name

Proper shipping name (ADR/RID) AEROSOLS, FLAMMABLE

Proper shipping name (IMDG) AEROSOLS, FLAMMABLE

Proper shipping name (ICAO) AEROSOLS, FLAMMABLE

Proper shipping name (ADN) AEROSOLS, FLAMMABLE

14.3. Transport hazard class(es)

ADR/RID class	2.1
ADR/RID classification code	5F
ADR/RID label	2.1
IMDG class	2.1
ICAO class/division	2.1
ADN class	2.1

Transport labels**14.4. Packing group**

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

EmS	F-D, S-U
ADR transport category	2
Tunnel restriction code	(D)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

PDF1 / DDF1

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

National regulations	The Aerosol Dispensers Regulations 2009 (SI 2009 No. 2824).
EU legislation	Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended). Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended). Council Directive of 20 May 1975 on the approximation of the laws of the Member States relating to aerosol dispensers (75/324/EEC) (as amended). Directive 2008/98/EC of the European Parliament and of the Council of 19 November 2008 on waste.

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision date	25/02/2019
Revision	1
SDS number	7638
Hazard statements in full	H220 Extremely flammable gas. H222 Extremely flammable aerosol. H229 Pressurised container: may burst if heated. H280 Contains gas under pressure; may explode if heated.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.