

Actuator

14-
810.910



<https://eao.com/p/14-810.910>

Your product:



14-810.910 Actuator

FRONT

Front dimension:	Ø 35 mm
Front bezel material:	Aluminium
Front bezel colour:	Black

MOUNTING

Design:	flush
----------------	-------

ELECTRICAL CHARACTERISTICS

Operating voltage:	24 V DC ± 10 %
Operation current:	mA

MECHANICAL CHARACTERISTIC

Tightening torque:	Fixing nut max. 0.25 Nm
Terminal:	Plug-in terminal, 2.8 x 0.5 mm
Weight:	0.016 kg

ACOUSTICAL CHARACTERISTICS

Tone frequency:	Approx. 3.2 kHz continuous tone only
------------------------	--------------------------------------

AMBIENT CONDITION

IP front protection:	IP65, according to DIN EN 60529
Operating temperature:	- 25 °C ... + 55 °C

Storage temperature: - 40 °C ... + 85 °C

CERTIFICATE

Approbations: CQC, EMC

Conformities: CE, UKCA, 2011 / 65 / EC (RoHS), 2014 / 35 / EU (LVD)


OTHER

Short Description: Actuator, Ø 35 mm, Black, Aluminium, anodised, Plug-in terminal, 2.8 x 0.5 mm, IP65, according to DIN EN 60529


Buzzer system: Piezo disc

Hints: For PCB application use print adator

Mounting cut-outs:



Wiring diagrams:



Dimension drawings:

