




Part Number : [1204063001](#)
Product Description : Ultra-Lock 2.0 (M12) Receptacle, 4 Poles, Female (Straight) to Leads, D-Coded, Back Panel Mount, M16 Mounting Threads, 0.30m (11.81") Length
Series Number : 120406
Status : Active
Product Category : Circular Industrial Connectors
Engineering Number : ERYA2U40E03C300



Documents & Resources

Drawings
[Drawing 1204063001_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead; Lead monoxide per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

ZZCERT_CE - Declaration of Conformity : CER_4000430755_00_000.pdf

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120406
Description	Ultra-Lock 2.0 (M12) Receptacle, 4 Poles, Female (Straight) to Leads, D-Coded, Back Panel Mount, M16 Mounting Threads, 0.30m (11.81") Length
IP Rating	IP67
Product Family	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock 2.0 (M12)
Type	Single Ended (pigtail)
UPC	195842274921

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Physical

Coupling Type	Internal Thread Push to Lock
Gender	Female
Keyway	D-coded
Length	0.30m
Material - Component	Nickel-plated Brass
Mounting Thread Size	M16
Net Weight	34.439/g
Orientation	Straight
Panel Mount	Back
Poles	4
Temperature Range - Operating	-40° to +85°C

Wire/Cable Type	Leads, UL 1569
Wire Size (AWG)	22

This document was generated on Sep 27, 2023