KERN PCB 6000-0-2023e



The standard in the laboratory, ideal for a wide range of applications for Industry $4.0\,$



Category			
Brand	KERN		
Product categoriy	Laboratory balance		
Product group	Precision balance		
Product family	PCB		
Measuring System			
Construction type of the scale	Single-range balance		
Weighing system	Strain gauge		
Weighing capacity [Max]	6000 g		
Readability [d]	1 g		
Resolution	6.000		
Linearity	± 2 g		
Reproducibility	1 g		
Default unit	g		
Units	kg g dwt tl (Tw) tl (HK) ozt tl (Singap, Malays) ct mo lb oz ffa m		
Adjustment options	Adjusting with external weight		
Recommended adjusting weight	5 kg (M2); 1 kg (M2)		
Possible calibration points	1,5 kg; 3 kg; 6 kg		
Stabilization time	3 s		

Warm-up time	30 min			
Eccentric loading at 1/3 [Max]	3 g			
Maximum creep (15 minutes)	4 g			
Maximum creep (30 minutes)	8 g			
A				
Approval				
CE mark	1			
Display				
Display type	LCD			
Display screen size	89×30 mm			
Display backlight	1			
Display digit height	21 mm			
Languages of the user interface	English			
0.0	Symbol language			
Construction				
Dimension housing (W×D×H)	163×245×65 mm			
Material display housing	Plastics			
Material housing	plastic			
Material weighing plate	stainless steel			
Material platform	Stainless steel			
Dimensions weighing surface (W×D)	150×170 mm			
Transport safety lock - bolt torque	0,4 Nm			
Levelling feet adjustable	✓			
Functions				
Number of keys for operation	5			
Auto-off interval(s) in mains power mode	off			
Auto-off interval(s) in battery	5 min 2 min 1 min			
mode/rechargeable battery mode	30 min 60 min 30 sec			
PreTare function	✓			
Tare function	manual (multi)			
Percentage determination	1			
Counting function	1			
Tolerance weighing	✓			
Tolerance weighing - type of signal	acoustically visual			
Function for averaging under unstable weighing conditions	✓			
Recipe/summing level	Rez A (Net total)			

KERN PCB 6000-0-2023e



The standard in the laboratory, ideal for a wide range of applications for Industry 4.0

Underfloor weighing	Hook (included in delivery)		
Interfaces	RS-232 (optional) Bluetooth (optional) Ethernet (optional) USB-Device (optional) KUP WiFi (optional)		
IP protection - display	no IP protection		
Counting			
Smallest piece weight when piece counting - laboratory conditions	2 g		
Smallest piece weight when piece counting - normal conditions	20 g		
Counting reference weight can be entered	1		
Reference quantity	5, 10, 20, 50, free, Input		
Counting resolution (laboratory conditions)	3.000		

Power Supply

Fower Supply				
Input voltage power supply / power [Max]	100 V - 240 V AC, 50 / 60 Hz			
Input voltage device / power [Max]	5,9V, 1A			
Plug-in power supply type	Power adapter			
Supplied power supply	Power supply unit			
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH			
Plug-in power supply / adapter for countries - optional	EURO UK US CH			
Rechargeable battery optional	Rchrg. battery optional - intern			
Rechargeable battery charging time	8 h			
Rechargeable battery operating time - backlight on	24 h			
Rechargeable battery operating time - backlight off	48 h			
Battery	4×1.5 V AA			
Battery / accumulator type	Li-Ion			
Battery connection	Battery insert			
Battery operating time	20 h			

80 %

Environmental conditions

Humity of environment [Max]

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Packing & Shipping

Readability force [d] (N)	1 d			
Dimensions packaging (W×D×H)	235×365×175 mm			
Net weight	1,457 kg			
Shipping method	Parcel service			
Net weight approx.	1,6 kg			
Gross weight approx.	2,4 kg			
Shipping weight	3 kg			
Services (optional)				
Article number for adjustment at	961-248			

the location of installation	901-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity (verification)	969-517

Pictograms

STANDARD



OPTION

Ĩ	• 6886. •	•	*	((1-	五		DAkkS
ET	RS 232	USB	BT	WLAN	LAN	ACCU	+3 DAYS