


Product Code: QCGM16WHT

Description: 16mm Nylon Glands - White



Dimensions

Spanner Size (mm)	22
Threaded Diameter (mm)	16
Threaded Entry Length (mm)	15.5

General Information

Colour	White
Cable Clamping Range (mm)	5 - 10
Recommended Cap Tightening Torque (Nm)	2.0 - 2.5
Ingress Protection	IP68
Temperature Rating (°C)	0 to +80

Materials

Gland Body: Nylon 66
 Seal: TPE (Thermoplastic Elastomer)
 Washer: PVC (Polyvinyl Chloride)

Standards

ANSI/UL 514B
 BS EN 60529: 1992 + A2: 2013