



Ultimate Industrial

HEARING PROTECTION RANGE



TECHNICAL PRODUCT DATASHEET

EAR PLUGS



UPDATED: 10/10/2019

EP301CD Detectable Earplug

Blue Foam PU Corded Detectable Earplug SNR 39

Ultraform™ PU Foam corded Earplugs provide an exceptional and individual fit. Simple fit design for quick and effective use. Individually packed in pairs for hygiene and easy distribution. High attenuation designed for enhanced noise protection in louder environments. Corded variation allows for the ear plugs to be conveniently hung around the neck when not required and easily re-inserted when necessary. Metal ball-bearing detected by automated inspection. Box contains 200 individually packed pairs for easy dispense.

Also available in non-detectable corded and un-corded.



SNR **39dB**
HIGH

ULTRAFORM
PRECISE FIT

METAL
DETECTABLE

FEATURES AND TECHNOLOGY



ULTRAFORM™
PRECISE FIT



INSULATING
PU FOAM



INDIVIDUALLY
PACKED



CORDED
DESIGN



HIGH
ATTENUATI
ON

TYPICAL INDUSTRIES



AUTOMOTIVE



DEMOLITION /
CONSTRUCTION



LEISURE
INDUSTRY



MANUFACTURING



FOOD
PROCESSING

TECHNICAL INFORMATION

ORDER REF #	EA/UC/PLUGS-EP301CD	
MATERIAL	FOAM PU	
PACKING	PER PACK: 1 BOX	PER CASE: 10
SIZE	ONE SIZE	
EU TYPE CERTIFICATION AND ONGOING CONFORMITY PERFORMED BY	INSPEC International Limited, 56 Leslie Hough Way, Salford, Greater Manchester, M6 6AJ, United Kingdom. Notified Body No. 01	

CERTIFICATION AND STANDARDS (SEE OVERLEAF FOR FURTHER DETAILS)

EN352-2:2002



ATTENUATION DATA



Phone: +44 (0)1902 451 451

Fax: +44 (0)1902 451 271

Email:

sales@ultimateindustrial.co.uk



Leadership in PROTECTION.™

© 2019. Ultimate Cleaners (Industrial) Ltd.
Victoria House, Colliery Road, Wolverhampton, WV1 2RD, UK.
Registered in England No. 2035621



Ultimate Industrial

HEARING PROTECTION RANGE



TECHNICAL PRODUCT DATASHEET

EAR PLUGS



UPDATED: 10/10/2019

ATTENUATION DATA:

Frequency (Hz)	125	250	500	1000	2000	4000	8000
Mean Attenuation (dB)	34.7	36.6	41.4	41.6	39.2	42.4	46
Standard Deviation (dB)	5.6	5.4	5.3	4	2.8	4.3	4.2
APV-Value (dB)	29.2	31.2	36.1	37.5	36.4	38	41.8

Nominal Diameter: 7mm-12mm
SNR: 39dB H:38dB M:37dB L:34dB

All measurements made in accordance with EN 352-2:2002. Assumed protection rounded to one decimal place were applicable.

FURTHER INFORMATION

STORAGE / TRANSPORT: Keep away from direct sunlight; store in a cool dry place. During transportation, ensure the product is well packaged to prevent damage. Store in their original packaging.

PRECAUTIONS BEFORE USE: It is very important that the fitting instructions and recommendations are adhered to. If not the protection offered will be seriously impaired and serious injury may result. Further information should be sought from the manufacturer. The enclosed product information sheet should be read before use.

RECOMMENDATION: These ear plugs must be fitted in accordance with instructions given by the manufacturer. The ear plugs must be worn all the time the wearer is exposed to noise. Removing the ear plus for even a small amount of time could result in serious injury. Keep away from infants and small children.

REMOVAL INSTRUCTIONS:

1. Remove the ear plugs only after leaving the noisy environment. 2. Twist the earplug to break the seal and pull slowly from the ear. 3. Dispose of the used ear plug responsibly. This is a single use product - do not reuse.

Although the ear plugs can be recommended for protection against the harmful effects of impulse noise, the SINGLE NUMBER RATING (SNR) is based on the attenuation of continuous noise and may not be an accurate indicator of the protection attainable against impulsive noise such as gunfire. Consult the outer packaging, including user instruction and fitting instructions before use. Failure to follow the provided instructions may affect the products ability to protect against

For more information about this product, or to access the Declaration of Conformity or Product Certification, visit: <https://www.ultimateindustrial.co.uk/product/1127-EP301CD>

If appropriate to the product, EC/EU Declaration of Conformities, relevant certification and supporting documentation are available to access through your distributor, at the above web address(s) or by contacting UCI customer services quoting the product reference code. This document and any other statement provided herein by or on behalf of UCI are given for informational purposes and do not constitute a contractual agreement nor warranty of merchantability. UCI assumes no responsibility for the suitability or adequacy of an end user's selection of product for a specific purpose. The manufacturer reserves the right to make any modifications it deems necessary. All product and company names are trademarks™ or registered® trademarks of their respective holders. © UCI Limited, 2019



Phone: +44 (0)1902 451 451
Fax: +44 (0)1902 451 271
Email: sales@ultimateindustrial.co.uk

Ultimate Industrial | Leadership in PROTECTION.™

© 2019. Ultimate Cleaners (Industrial) Ltd.
Victoria House, Colliery Road, Wolverhampton, WV1 2RD, UK.
Registered in England No. 2035621