



Model No. M15EURDLF

64mm wide Excell® laminated steel padlock with 38mm long shackle

Best Used For:



Industrial,
Storefront &
Business Gates



Residential Gates &
Fences



Sheds, Workshops
& Garages



Self-Storage Units &
Lockers



Tools, Job Boxes &
Gang Boxes

Security Level:



Basic to medium
security:

Generally recommended for
indoor general purpose

Overview & Features

Product Features


- Tough-Cut? octagonal boron-carbide shackle is 50% harder than hardened steel
- 38mm shackle length for more uses
- Dual-Armor? protection: 64mm laminated steel core for strength surrounded by stainless steel & zinc outer components for weather resistance
- Dual ball bearing locking for maximum pry resistance
- Reinforced body bumper for scratch resistance
- 5-pin cylinder for increased pick resistance
- Limited Lifetime Warranty

Product Details

The Master Lock Excell® No. M15EURDLF Laminated Padlock features a 64mm wide laminated steel body for maximum strength and reliability, and is surrounded by stainless steel and zinc outer components for weather resistance. The 11mm diameter octagonal shackle is 38mm long and made of Tough-Cut™ boron-carbide, 50% harder than hardened steel, offering maximum resistance to cutting and sawing. The 5-pin cylinder prevents picking and the dual locking ball bearings provide maximum resistance against prying and hammering. The Limited Lifetime Warranty provides peace of mind from a brand you can trust.

Product Specifications

Product Number	M15EURDLF
Body Width	64mm
Shackle Dimensions	A: 11mm B: 38mm C: 36mm
Colour	Silver
Description	Keyed Different
Shelf Pack Qty	4
Master Carton Qty	24



Master Lock Europe S.A.S.

10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu