

Category 8 contractor grade 8p8c STP Plug:



Category 6A/7/8 8p8c STP Plug (PEScb):

This high performance fully shielded contractor grade Category 8 plug offers quick and reliable termination.

Features:

- 2 part shielded plug
- Performs to Category 8 at channel level
- 3 prong contacts
- Suitable for solid and stranded category 8 cable up to 8mm and cores between 1.16 and 1.45mm O.D.
- Backwards compatible for Category 6A and Category 7
- Suitable for termination with TUK's specialist single-action crimp tool for XL cable (T23PGSXL) <https://tuk.co.uk/product/modular-crimp-tool-for-xl-cable> or our ratchet crimp tool (TR2076) Ratchet Crimp Tool For Extra Large Shielded Cable – TUK Ltd
- For use with strain relief boot PS2**8 <https://tuk.co.uk/product/strain-relief-over-boots/>
- PoE+ Compliant

Specifications:

- Weight including packaging: 154g (packed in 50s)
Weight of individual plug: 3g
- Dimensions:
Plug: 21.6 x 11.8 x 8mm
Plug with cable grip extended: 29.6 x 11.8 x 8mm
- Colour: silver

- **Materials:**
Housing: Polycarbonate UL-94V0
Shell: Nickel-plated Brass
Contacts: 50µ"/1.27µm gold plated

Packaging: Supplied in bags of 50 then in bags of 500's

Commodity code: 85444920


EAN: 5055386511157

Country of Origin: China




 PEScb - Assembly Instructions

1. Insert boot and strip 30mm sheath from the cable.




2. Straighten wires, then slide into insert and trim.



3. Cut off surplus wires.



4. Slide assembly into plug body and push cable until it stops.



5. Crimp.



6. After crimping.




7. Gently crimp shielding clamp (excess pressure will cause deformation).



8. Assembly process complete.

ROHS Compliant

Code: PEScb



3 prong contacts

