

Satellite Surge Protector multicomp^{PRO}



Features

- Impedance: 75Ω
- F-Type Male to Female Connector

Specification Table

Characteristics		Typical Value	Q.C. Limit
Frequency Range	1G	5 ~ 1000MHz	
	2G	1000MHz ~ 2400MHz	
Input		1 IN (F-Type Male Connector)	
Output		1 OUT (F-Type Female Connector)	
Insertion Loss	1G	0.8dB	≤ 1dB
	2G	1.2dB	≤ 1.5dB
Return Loss		12dB	≥ 10dB
Max. Operating Voltage and Current		1A @ 25V DC	
DC Breakdown Voltage 100V/s		230 ±42V	
Impulse Spark-Over Voltage 1kV/μs		≤ 800V	
Impulse Discharge Current 8/20μs		8KA	

Part Number Table

Description	Part Number
Satellite Surge Protector, 75Ω	33-10400

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp^{PRO}