

Aluminum Capacitors Radial Miniature, High Voltage





Fig.1 Component outline



FEATURES

- Polarized aluminum electrolytic capacitors, non-solid electrolyte
- Radial leads, cylindrical aluminum case, insulated with a blue vinyl sleeve
- Pressure relief
- Charge and discharge proof
- Miniaturized, ultra high CV-product per unit volume
- Long useful life:
3000 to 4000 h at 105 °C, high reliability
- Lead (Pb)-Free versions are RoHS compliant


**RoHS
COMPLIANT**

APPLICATIONS

- High-reliability and professional applications
- Lighting, monitors, consumer electronics, general industrial
- Filtering of high voltages in power supplies

MARKING

The capacitors are marked (where possible) with the following information:

- Rated capacitance value (in μF)
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (M for $\pm 20\%$)
- Rated voltage (in V)
- Date code, in accordance with IEC 60062
- Code indicating factory of origin
- Name of manufacturer
- Upper category temperature (105 °C)
- Negative terminal identification
- Series number (152)

QUICK REFERENCE DATA	
DESCRIPTION	VALUE
Nominal case sizes ($\varnothing D \times L$ in mm)	10 x 12 to 18 x 35
Rated capacitance range, C_R	1.0 to 220 μF
Tolerance on C_R	$\pm 20\%$
Rated voltage range, U_R	200 to 450 V
Category temperature range	- 40 to + 105 °C
Endurance test at 105 °C	2000 hours
Useful life at 105 °C:	
Case $\varnothing D = 10$ and 12.5 mm	3000 hours
Case $\varnothing D = 16$ and 18 mm	4000 hours
Useful life at 40 °C, $1.6 \times I_R$ applied:	
Case $\varnothing D = 10$ and 12.5 mm	200 000 hours
Case $\varnothing D = 16$ and 18 mm	260 000 hours
Shelf life at 0 V, 105 °C	1000 hours
Based on sectional specification	IEC 60384-4/EN 130300
Climatic category IEC 60068	40/105/56

SELECTION CHART FOR C_R , U_R AND RELEVANT NOMINAL CASE SIZES ($\varnothing D \times L$ in mm)				
C_R (μF)	U_R (V)			
	200	250	400	450
1.0	-	-	-	10 x 12
2.2	-	-	10 x 12	10 x 16
4.7	-	-	10 x 16	10 x 20
	-	-	10 x 12	-
6.8	-	-	10 x 16	12.5 x 20
10	10 x 12	10 x 16	10 x 20	12.5 x 20
	10 x 16	12.5 x 20	12.5 x 25	16 x 25
22	-	-	16 x 20	18 x 20
	10 x 20	12.5 x 20	16 x 20	16 x 35
33	-	-	-	18 x 25
	12.5 x 20	12.5 x 25	16 x 25	18 x 35
47	-	16 x 20	-	-
	12.5 x 25	-	16 x 35	-
100	16 x 20	16 x 25	18 x 35	-
220	16 x 35	-	-	-

DIMENSIONS in millimeters, **AVAILABLE FORMS**




Fig.2 Form CA: Long leads




Fig.3 Form CB: Cut leads




Fig.4 Form TFA: Taped in box (ammopack)

Table 1

DIMENSIONS in millimeters, MASS AND PACKAGING QUANTITIES									
NOMINAL CASE SIZE Ø D x L	CASE CODE	Ø D	Ø D _{max.}	L _{max.}	F	MASS (g)	PACKAGING QUANTITIES		
							FORM CA	FORM CB	FORM TFA
10 x 12	14	0.6	10.5	13.5	5.0 ± 0.5	≈ 1.6	1000	500	800
10 x 16	15	0.6	10.5	17.5	5.0 ± 0.5	≈ 1.9	500	500	800
10 x 20	16	0.6	10.5	22.0	5.0 ± 0.5	≈ 2.2	500	500	800
12.5 x 20	17	0.6	13.0	22.0	5.0 ± 0.5	≈ 4.0	500	500	500
12.5 x 25	18	0.6	13.0	27.0	5.0 ± 0.5	≈ 5.0	250	250	500
16 x 20	19a	0.8	16.5	22.0	7.5 ± 0.5	≈ 6.0	250	250	250
16 x 25	19	0.8	16.5	27.0	7.5 ± 0.5	≈ 8.0	250	250	250
16 x 35	21	0.8	16.5	37.5	7.5 ± 0.5	≈ 11.0	100	100	-
18 x 20	1820	0.8	18.5	22.0	7.5 ± 0.5	≈ 8.0	100	100	-
18 x 25	1825	0.8	18.5	27.0	7.5 ± 0.5	≈ 10.0	100	100	-
18 x 35	22	0.8	18.5	37.5	7.5 ± 0.5	≈ 14.5	100	100	-

Note

1. Detailed tape dimensions see section 'PACKAGING'.



ELECTRICAL DATA	
SYMBOL	DESCRIPTION
C_R	rated capacitance at 100 Hz, tolerance $\pm 20\%$
I_R	rated RMS ripple current at 100 Hz, 105 °C
I_{L1}	max. leakage current after 1 minute at U_R
$\tan \delta$	max. dissipation factor at 100 Hz
Z	max. impedance at 10 kHz

Note

Unless otherwise specified, all electrical values in Table 2 apply at $T_{amb} = 20\text{ °C}$, $P = 86\text{ to }106\text{ kPa}$, $RH = 45\text{ to }75\%$.

ORDERING EXAMPLE

Electrolytic capacitor 152 series
4.7 $\mu\text{F}/400\text{ V}$; $\pm 20\%$
Nominal case size: $\varnothing 10 \times 16\text{ mm}$; Form TFA

Ordering Code: MAL215236478E3
Former 12NC: 2222 152 36478

Table 2

ELECTRICAL DATA AND ORDERING INFORMATION									
U_R (V)	C_R 100 Hz (μF)	NOMINAL CASE SIZE $\varnothing D \times L$ (mm)	I_R 100 Hz 105 °C (mA)	I_{L1} 1 min (μA)	$\tan \delta$ 100 Hz	Z 10 kHz (Ω)	ORDERING CODE MAL2152		
							BULK PACKAGING		TAPED
							FORM CA	FORM CB	FORM TFA
200	10	10 x 12	85	130	0.12	6.3	52109E3	62109E3	32109E3
	22	10 x 16	120	202	0.12	3.2	52229E3	62229E3	32229E3
	33	10 x 20	150	268	0.12	2.3	52339E3	62339E3	32339E3
	47	12.5 x 20	240	352	0.12	0.9	52479E3	62479E3	32479E3
	68	12.5 x 25	310	478	0.12	0.6	52689E3	62689E3	32689E3
	100	16 x 20	340	670	0.12	0.4	52101E3	62101E3	32101E3
	220	16 x 35	630	1390	0.12	0.2	52221E3	62221E3	-
250	10	10 x 16	105	145	0.12	6.3	53109E3	63109E3	33109E3
	22	12.5 x 20	180	235	0.12	2.3	53229E3	63229E3	33229E3
	33	12.5 x 20	180	318	0.12	1.5	53339E3	63339E3	33339E3
	47	12.5 x 25	310	423	0.12	0.9	53479E3	63479E3	33479E3
	47	16 x 20	310	423	0.12	0.9	93475E3	93476E3	93473E3
	100	16 x 25	340	820	0.12	0.4	53101E3	63101E3	33101E3
400	2.2	10 x 12	44	96	0.15	28.0	56228E3	66228E3	36228E3
	4.7	10 x 12	48	127	0.15	24.0	96475E3	96476E3	96473E3
	4.7	10 x 16	65	126	0.15	18.0	56478E3	66478E3	36478E3
	6.8	10 x 16	65	152	0.15	12.0	56688E3	66688E3	36688E3
	10	10 x 20	80	190	0.15	9.0	56109E3	66109E3	36109E3
	22	12.5 x 25	150	334	0.15	3.8	56229E3	66229E3	36229E3
	22	16 x 20	150	334	0.15	3.8	96225E3	96226E3	96223E3
	33	16 x 20	190	466	0.15	2.6	56339E3	66339E3	36339E3
	47	16 x 25	240	634	0.15	2.0	56479E3	66479E3	36479E3
	68	16 x 35	310	886	0.15	1.7	56689E3	66689E3	-
100	18 x 35	380	1270	0.15	0.9	56101E3	66101E3	-	
450	1.0	10 x 12	30	67	0.20	94.0	57108E3	67108E3	37108E3
	2.2	10 x 16	50	99	0.20	26.0	57228E3	67228E3	37228E3
	4.7	10 x 20	65	133	0.20	20.0	57478E3	67478E3	37478E3
	6.8	12.5 x 20	80	162	0.20	16.0	57688E3	67688E3	37688E3
	10	12.5 x 20	90	205	0.20	10.0	57109E3	67109E3	37109E3
	22	16 x 25	150	367	0.20	4.6	57229E3	67229E3	37229E3
	22	18 x 20	150	367	0.20	4.6	97225E3	97226E3	-
	33	16 x 35	200	516	0.20	3.4	57339E3	67339E3	-
	33	18 x 25	200	516	0.20	3.4	97335E3	97336E3	-
	47	18 x 35	260	705	0.20	2.0	57479E3	67479E3	-



ADDITIONAL ELECTRICAL DATA		
PARAMETER	CONDITIONS	VALUE
Voltage		
Surge voltage	$U_R = 200$ to 250 V	$U_s \leq 1.15 \times U_R$
	$U_R = 400$ to 450 V	$U_s \leq 1.10 \times U_R$
Reverse voltage		$U_{rev} \leq 1$ V
Current		
Leakage current	After 1 minute at U_R	$I_{L1} \leq 0.03 C_R \times U_R + 70 \mu A$
	After 5 minutes at U_R	$I_{L5} \leq 0.015 C_R \times U_R + 30 \mu A$
Inductance		
Equivalent series inductance (ESL)	Case $\varnothing D = 10$ mm	typ. 16 nH
	Case $\varnothing D \geq 12.5$ mm	typ. 18 nH
Resistance		
Equivalent series resistance (ESR)	Calculated from $\tan \delta_{max.}$ and C_R (see Table 2)	$ESR = \tan \delta / 2 \pi f C_R$

Table 3

MULTIPLIER OF RIPPLE CURRENT (I_R)		
FREQUENCY (Hz)	I_R MULTIPLIER	
	$U_R \leq 250$ V	$U_R > 250$ V
50	0.75	0.75
100	1.00	1.00
300	1.50	1.30
1000	2.00	1.60
3000	2.20	1.90
10 000	2.50	2.20
$\geq 100\ 000$	3.00	2.50

RIPPLE CURRENT AND USEFUL LIFE

I_A = actual ripple current at 100 Hz
 I_R = rated ripple current at 100 Hz, 105 °C
 (1) Useful life at 105 °C and I_R applied
 case $\varnothing D = 10$ and 12.5 : 3000h
 case $\varnothing D = 16$ and 18 : 4000h




Fig.5 Multiplier of useful life as a function of ambient temperature and ripple current load



Table 4

TEST PROCEDURES AND REQUIREMENTS			
TEST		PROCEDURE (quick reference)	REQUIREMENTS
NAME OF TEST	REFERENCE		
Endurance	IEC 60384-4/ EN130300 subclause 4.13	$T_{amb} = 105\text{ }^{\circ}\text{C}$; U_R applied; 2000 h	$\Delta C/C: \pm 20\%$ $\tan \delta \leq 2 \times \text{spec. limit}$ $Z \leq 2 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$
Useful life	CECC 30301 subclause 1.8.1	$T_{amb} = 105\text{ }^{\circ}\text{C}$; U_R and I_R applied; case $\emptyset D = 10$ and 12.5: 3000 h case $\emptyset D = 16$ and 18: 4000 h	$\Delta C/C: \pm 50\%$ $\tan \delta \leq 3 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ no short or open circuit total failure percentage: $\leq 1\%$
Shelf life (storage at high temperature)	IEC 60384-4/ EN130300 subclause 4.17	$T_{amb} = 105\text{ }^{\circ}\text{C}$; no voltage applied; 1000 h after test: U_R to be applied for 30 min, 24 to 48 h before measurement	$\Delta C/C: \pm 20\%$ $\tan \delta \leq 2 \times \text{spec. limit}$ $Z \leq 2 \times \text{spec. limit}$ $I_{L5} \leq 2 \times \text{spec. limit}$
Reverse voltage	IEC 60384-4/ EN130300 subclause 4.15	$T_{amb} = 105\text{ }^{\circ}\text{C}$: 125 h at $U = -1\text{ V}$, followed by 125 h at U_R	$\Delta C/C: \pm 15\%$ $I_{L5} \leq \text{spec. limit}$ $\tan \delta \leq \text{spec. limit}$



Disclaimer

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.