





**RoHS
Compliant**




Specification

Waterproof Rate	: IP66
Test Conditions	
Current Rating	: 5A+2A
Temperature Range	: -20°C to +80°C
Conduct Resistance	: 50mΩ Max.
Hi-Pot Test	: 500V AC, 5mA (1Minute)
Insulation Resistance	: 100MΩ Min. By 500V DC

Diagram



PIN OUT



Pin Assignments
Front View

No.	Description	Qty.	Material	Plating & Color
A	Body	1	Plastic	Black
B	Female Pin	5	Brass	Gold Plating Over Nickel Plating
C	Liquid Glue	1	N/A	Black
D	Cap		Silicon	
E	Nut		Brass	Nickel Plating

Part Number Table

Description	Part Number
EV Charging Connector, Female Connector, 5A+2A, 5 Pins, IP66	MP013748

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.