





Coding pin

Circuit




Technical Data:

Case Material Cover	Vyncolit black
Base Plate	PA GF black
Switch Lever Material	PA GF red
Min. Insulation Resistance	100M Ω m
Dielectric Withstanding Voltage	1050V-1min.
Max. Contact Drop During Resistive Load	150mV
Voltage	up to 32VDC
Duty Rating (Continuous)	2x500A
Overload	2x2000A-1.5min. 2x2500A-10sec.


Auxiliary Contact:

Inrush Current	8A 12/24V
Continuous Current	3A 12/24V

Sealing	IP 67/ IEC 529
Vibration	10G/ 18-500Hz
Weight	750g/1.65 P
Temperature Range	-40°C to +100°C
Wire Section (at nominal Load Main Terminals)	min. 250mm ²
Switch Lever	not removeable lockable in "OFF" position not lockable in "ON" position
Max. Torque (Main Terminals)	18-22Nm



Date	Name	mm	Scale
06.11.2017	Seege	1:2	
13.11.2017	Grind	General Tolerances DIN ISO 2768 cL	



Drawing No:

35-524-231-R-A-908

NSN: