



Wire Protection & Management > Adhesives & Sealants > Epoxy Adhesives



Packaging Method: **Dual Pack**

Packaging Quantity: **5**

Heat Resistance Temperature (Max): **150 °C**

Features

Body Features

Color (Supplied)	Black, Gray
Material Systems Code	25

Usage Conditions

Heat Resistance Temperature (Max)	150 °C
-----------------------------------	--------

Packaging Features

Packaging Method	Dual Pack
Packaging Quantity	5

Other

Adhesives & Sealants Comment	2-Part Epoxy
Curing Method	20 °C for 24 hr, 85 °C for 1 hr
Pot Life	90 minute

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235)









Candidate List Declared Against: JUNE 2023 (235)
Does not contain REACH SVHC


Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 7662514004 HCTE-1500-0-SP	 TE Part # 2270594002 HCTE-1625-0-SP	 TE Part # 5470284010 CONVOLEX-1-0-SP	 TE Part # 5470234017 CONVOLEX-7/16-0-SP
 TE Part # 3774834004 HCTE-2000-0-SP	 TE Part # CL1665-001 S1125-APPLICATOR	 TE Part # 7730454002 HCTE-1250-0-SP	 TE Part # 3679754004 HCTE-1000-0-SP



TE Part # 1618474004
HCTE-0625-0-SP



TE Part # 8918194004
HCTE-0750-0-SP



TE Part # 6638954004
HCTE-0500-0-SP



TE Part # 6790994004
HCTE-0187-0-SP



TE Part # 5172334004
HCTE-0281-0-SP



TE Part # 7391174004
HCTE-0437-0-SP



TE Part # 5470014004
CONVOLEX-1-5/8-0-SP



TE Part # 9693274004
HCTE-1750-0-SP


Customers Also Bought



TE Part #NB13484001
RNF-100-3/4-YO-FSP




TE Part #ZPF000000000122826
983-6S 20-04 PN-A1301




TE Part #8-1437213-8
FSK-23B-15




TE Part #ZPF000000000006406
951-02H 8-4 P 50




TE Part #ZPF000000000104638
999-1-00 Y 13 F 04 PN 395




TE Part #30590003
TUBE F INOX_ 316L_ LG:35.5



TE Part #ZPF000000000003841
745-8040-10



TE Part #ZPF000000000202371
746-8025-08



TE Part #YDTS20Y17-06XN0000
HERM RECP



TE Part #AAC2388-00
PC4F0036-19NY-2-Z-L250-A

Documents



Product Drawings

S1125-KIT-1

English

Datasheets & Catalog Pages

Adhesives Selection Guide

English

Product Specifications

Product Specification

English

Thermofit Adhesive S-1125 Epoxy, Flexible

English

Product Environmental Compliance

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet

Safety Datasheet

Safety Datasheet



English

[Safety Datasheet](#)

Japanese

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

Japanese

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)



[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

German

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

French

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

[Safety Datasheet](#)

English

[Safety Datasheet](#)

English

[Safety Datasheet](#)

[Safety Datasheet](#)

Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English