



**Part Number :** [1203410812](#)

**Product Description :** Micro-Change (M12) Double-Ended Cordset, 8-Pole Male (Straight) to 4-Pole Female (Straight), 24 AWG, Teal TPE Cable, 1.0m (3.28') Length

**Series Number :** 120341

**Status :** Active

**Product Category :** Circular Industrial Cordsets

**Engineering Number :** E12A03004M010



---

## Documents & Resources

### Drawings

[Drawing 1203410812\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Circular Industrial Cordsets
Series	120341
Description	Micro-Change (M12) Double-Ended Cordset, 8-Pole Male (Straight) to 4-Pole Female (Straight), 24 AWG, Teal TPE Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Family	Brad Industrial Ethernet Solutions
Product Name	Micro-Change (M12)
Region	America, Asia, Europe
Type	Double Ended
UPC	78172556892

### Agency

UL	E361772
----	---------

### Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	50V AC / 60 DC

### Physical

Cable Diameter	6.10mm (.240")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Teal
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Multiple

LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	70.500/g
Orientation	Straight to Straight
Poles	4, 8
Temperature Range - Operating	-20° to +75°C
Wire/Cable Type	Unshielded TPE/AWM 2463
Wire Size (AWG)	24

---

This document was generated on Dec 24, 2023