

## Data Sheet



Lead (Pb) Free  
RoHS 6 fully  
compliant



### Description

This 1W Mini Power LED Light Source is a high performance energy efficient device which can handle high thermal and high driving current. Option with electrically isolated metal slug is also available.

The White Mini Power LED is available in the range of color temperature from 2700K to 10000K.

The low profile package design and ultra small footprint is suitable for a wide variety of applications especially where space and height is a constraint.

The package is compatible with reflow soldering process. To facilitate easy pick & place assembly, the LEDs are packed in EIA-compliant tape and reel.

### Features


- Available in Red, Red Orange, Amber, Blue, Royal Blue, Green, Cool White, Neutral White and Warm White color
- Small footprint
- Energy efficient
- Direct heat transfer from metal slug to mother board
- Compatible with reflow soldering process
- High current operation
- Long operation life
- Wide viewing angle
- Silicone encapsulation
- Non-ESD sensitive (threshold > 16kV)
- MSL 1 products

### Applications

- Architectural lighting
- Garden lighting
- Decorative lighting
- Sign backlight
- Safety, exit and emergency sign lightings
- Specialty lighting such as task lighting and reading lights
- Retail display
- Commercial lighting
- Accent or marker lightings, strip or step lightings
- Portable lightings, bicycle head lamp, torch lights.
- Pathway lighting
- Street lighting
- Tunnel lighting

**CAUTION:** Customer is advised to keep the LEDs in the MBB when not in use as prolonged exposure to environment might cause the silver plated leads to tarnish, which might cause difficulties in soldering.

## Package Dimensions




## Device Selection Guide ( $T_J = 25^\circ\text{C}$ )

Part Number	Color	Luminous Flux (Im) / Radiometric Power (mW), $\Phi_V^{[1,2]}$			Test Current (mA)	Dice Technology	Electrically Isolated Metal Slug
		Min.	Typ.	Max.			
ASMT-JR10-ARS01	Red	39.8	45.0	67.2	350	AllInGaP	No
ASMT-JA10-ARS01	Amber	39.8	45.0	67.2	350	AllInGaP	No
ASMT-JH10-ARS01	Red Orange	39.8	45.0	67.2	350	AllInGaP	No
ASMT-JB11-NLN01	Blue	10.7	15.0	23.5	350	InGaN	Yes
ASMT-JL11-NMP01	Royal Blue	225 mW	320 mW	435 mW	350	InGaN	Yes
ASMT-JG11-NST01	Green	51.7	70.0	87.4	350	InGaN	Yes
ASMT-JW11-NTT01	Cool White	67.2	70.0	87.4	350	InGaN	Yes
ASMT-JN11-NST01	Neutral White	51.7	65.0	87.4	350	InGaN	Yes
ASMT-JY11-NST01	Warm White	51.7	60.0	87.4	350	InGaN	Yes

### Notes:

1.  $\Phi_V$  is the total luminous flux / radiometric power output as measured with an integrating sphere at 25ms mono pulse condition.
2. Flux tolerance is  $\pm 10\%$ .

## Part Numbering System



Note:

1. Please refer to Page 9 for selection details.

## Absolute Maximum Ratings

Parameter	AllnGaP	InGaN	Units
DC Forward Current [1]	350	350	mA
Peak Pulsing Current [2]	1000	1000	mA
Power Dissipation	1085	1400	mW
Reverse Voltage	5	5	V
LED Junction Temperature	125	150	°C
Operating Metal Slug Temperature Range at 350 mA	-40 to +115	-40 to +135	°C
Storage Temperature Range	-40 to +120	-40 to +135	°C
Soldering Temperature	Refer to Figure 24		

Note:

1. Derate linearly based on Figure 7 for AlInGaP and Figure 17 for InGaN.
2. Pulse condition duty factor = 10%, Frequency = 1 kHz.

### Optical Characteristics at 350 mA (T<sub>J</sub> = 25 °C)

		Peak Wavelength, λ <sub>PEAK</sub> (nm)	Dominant Wavelength, λ <sub>D</sub> <sup>[1]</sup> (nm)	Viewing Angle, 2θ <sub>½</sub> <sup>[2]</sup> (°)	Luminous Efficiency (lm/W)
Part Number	Color	Typ.	Typ.	Typ.	Typ.
ASMT-JR10-ARS01	Red	635	625	165	54
ASMT-JA10-ARS01	Amber	598	590	165	54
ASMT-JH10-ARS01	Red Orange	625	615	165	54
ASMT-JG11-NST01	Green	519	525	165	57
ASMT-JB11-NLN01	Blue	460	470	165	12
ASMT-JL11-NMP01	Royal Blue	450	455	165	Not applicable

		Correlated Color Temperature, CCT (Kelvin)	Viewing Angle, 2θ <sub>½</sub> <sup>[2]</sup> (°)	Luminous Efficiency (lm/W)
Part Number	Color	Min.	Max.	Typ.
ASMT-JW11-NTT01	Cool White	4500	10000	140
ASMT-JN11-NST01	Neutral White	3500	4500	140
ASMT-JY11-NST01	Warm White	2700	3500	140

Notes:

1. The dominant wavelength, λ<sub>D</sub>, is derived from the CIE Chromaticity Diagram and represents the color of the device.
2. θ<sub>½</sub> is the off-axis angle where the luminous intensity is ½ the peak intensity.

### Electrical Characteristic at 350 mA (T<sub>J</sub> = 25°C)

	Forward Voltage, V <sub>F</sub> (Volts) at I <sub>F</sub> = 350mA			Thermal Resistance, R <sub>θj-ms</sub> (°C/W) <sup>[1]</sup>
Dice Type	Min.	Typ	Max.	Typ.
AllnGaP	1.9	2.4	3.1	9
InGaN	2.8	3.5	4.0	9

Note:

1. R<sub>θj-ms</sub> is Thermal Resistance from LED junction to metal slug.

## AllnGaP




Figure 1. Relative Intensity vs. Wavelength for Red, Red-Orange and Amber




Figure 2. Relative Luminous Flux vs. Mono Pulse Current




Figure 3. Forward Current vs. Forward Voltage




Figure 4. Radiation Pattern for Red, Red Orange and Amber




Figure 5. Maximum pulse current vs. ambient temperature.  
Derated based on  $T_A = 25^\circ\text{C}$ ,  $R\theta_{J-A} = 50^\circ\text{C/W}$ .




Figure 6. Maximum pulse current vs. ambient temperature.  
Derated based on  $T_A = 85^\circ\text{C}$ ,  $R\theta_{J-A} = 50^\circ\text{C/W}$ .

## AllInGaP




Figure 7. Relative Light Output vs. Junction Temperature




Figure 8. Forward Voltage Shift vs. Junction Temperature




Figure 9. Maximum Forward Current vs. Ambient Temperature. Derated based on  $T_{JMAX} = 125\text{°C}$ ,  $R\theta_{J-A} = 30\text{°C/W}$ ,  $40\text{°C/W}$  and  $50\text{°C/W}$




Figure 10. Maximum Forward Current vs. Ambient Temperature. Derated based on  $T_{JMAX} = 125\text{°C}$ ,  $R\theta_{J-MS} = 9\text{°C/W}$

## InGaN




Figure 11. Relative Intensity vs. Wavelength for Cool and Warm White




Figure 12. Relative Intensity vs. Wavelength for Blue, Royal Blue and Green




Figure 13. Relative Luminous Flux vs. Mono Pulse Current




Figure 14. Forward Current vs. Forward Voltage




Figure 15. Radiation Pattern for Blue, Royal Blue and Green




Figure 16. Radiation Pattern for Cool White, Neutral White and Warm White




Figure 17. Maximum pulse current vs. ambient temperature.  
Derated based on  $T_A = 25^\circ\text{C}$ ,  $R\theta_{J-A} = 50^\circ\text{C}/\text{W}$ .




Figure 18. Maximum pulse current vs. ambient temperature.  
Derated based on  $T_A = 85^\circ\text{C}$ ,  $R\theta_{J-A} = 50^\circ\text{C}/\text{W}$ .

## InGaN




Figure 19. Relative Light Output vs. Junction Temperature




Figure 20. Forward Voltage Shift vs. Junction Temperature




Figure 21. Maximum Forward Current vs. Ambient Temperature. Derated based on  $T_{JMAX} = 150^\circ\text{C}$ ,  $R\theta_{J-A} = 30^\circ\text{C}/\text{W}$ ,  $40^\circ\text{C}/\text{W}$  and  $50^\circ\text{C}/\text{W}$




Figure 22. Maximum Forward Current vs. Metal Slug Temperature. Derated based on  $T_{JMAX} = 150^\circ\text{C}$ ,  $R\theta_{J-MS} = 9^\circ\text{C}/\text{W}$ .




Figure 23. Recommended soldering land pattern




Figure 24. Recommended Reflow Soldering Profile

Note: For detail information on reflow soldering of Avago surface mount LEDs, do refer to Avago Application Note AN 1060 Surface Mounting SMT LED Indicator Components.

## Option Selection Details

ASMT-Jx1x – x x<sub>1</sub> x<sub>2</sub> x<sub>3</sub> x<sub>4</sub>

x<sub>1</sub> – Minimum Flux Bin Selection

x<sub>2</sub> – Maximum Flux Bin Selection

x<sub>3</sub> – Color Bin Selection

x<sub>4</sub> – Packaging Option

## Flux Bin Limit [x<sub>1</sub> x<sub>2</sub>]

Color	Bin ID	Luminous Flux (lm) / Radiometric Power (mW) at 350 mA	
		Min.	Max.
Blue	K	8.2	10.7
	L	10.7	13.9
	M	13.9	18.1
	N	18.1	23.5
Other Colors	Q	30.6	39.8
	R	39.8	51.7
	S	51.7	67.2
	T	67.2	87.4
Royal Blue	M	225	275
	N	275	355
	P	355	435

Tolerance for each bin limits is ±10%

## Color Bin Selection [x<sub>3</sub>]

Individual reel will contain parts from one full bin only.

### Cool White

0	Full Distribution
E	VM, UM, VN and UN
F	WM, VM, WN and VN
G	XM, WM, XN and WN
H	UN, VN, U0 and V0
J	WN, VN, W0 and V0
K	XN, WN, X0 and W0
L	V0, U0, VP and UP
M	W0, V0, WP, VP and WQ
N	X0, W0, XP, WP and WQ
P	Y0
Q	YA

### Neutral White

0	Full Distribution
E	SM, RM, S1 and R1
F	TM, SM, TN and S1
G	S1, R1, S0 and R0
H	TN, S1, T0 and S0
J	S0, R0, SA and RA
K	T0, S0, TP and SA




Figure 25. Color bin Structure for Cool White

### Warm White

0	Full Distribution
E	NM, MM, N1 and M1
F	PM, NM, P1 and N1
G	QM, PM, Q1 and P1
H	M1, N1, M0 and N0
J	P1, N1, P0 and N0
K	Q1, P1, Q0 and P0
L	N0, M0, NA and MA
M	P0, N0, PA and NA
N	Q0, P0, QA and PA

### Others Colors

0	Full Distribution
Z	A and B
Y	B and C
W	C and D
V	D and E
Q	A, B and C
P	B, C and D
N	C, D and E
M	D, E and F




Figure 26. Color bin structure for Warm White




Figure 27. Color bin structure for Neutral White

## Color Bin Limits

Cool White	Color Limits (Chromaticity Coordinates)				
Bin UM	x	0.365	0.348	0.347	0.367
	y	0.386	0.385	0.372	0.400
Bin UN	x	0.365	0.362	0.346	0.347
	y	0.386	0.372	0.359	0.372
Bin U0	x	0.362	0.360	0.344	0.346
	y	0.372	0.357	0.344	0.359
Bin UP	x	0.360	0.357	0.343	0.344
	y	0.357	0.342	0.331	0.344
Bin VM	x	0.329	0.329	0.348	0.347
	y	0.357	0.369	0.385	0.372
Bin VN	x	0.329	0.329	0.347	0.346
	y	0.345	0.357	0.372	0.359
Bin V0	x	0.329	0.329	0.346	0.344
	y	0.331	0.345	0.359	0.344
Bin VP	x	0.329	0.344	0.343	0.329
	y	0.331	0.344	0.331	0.320
Bin WM	x	0.329	0.329	0.315	0.314
	y	0.369	0.357	0.344	0.355
Bin WN	x	0.329	0.316	0.315	0.329
	y	0.345	0.333	0.344	0.357
Bin W0	x	0.329	0.329	0.317	0.316
	y	0.345	0.331	0.320	0.333
Bin WP	x	0.329	0.329	0.318	0.317
	y	0.331	0.320	0.310	0.320
Bin WQ	x	0.329	0.329	0.319	0.318
	y	0.320	0.310	0.300	0.310
Bin XM	x	0.301	0.314	0.315	0.303
	y	0.342	0.355	0.344	0.333
Bin XN	x	0.305	0.303	0.315	0.316
	y	0.322	0.333	0.344	0.333
Bin X0	x	0.308	0.305	0.316	0.317
	y	0.311	0.322	0.333	0.320
Bin XP	x	0.308	0.317	0.319	0.311
	y	0.311	0.320	0.300	0.293
Bin YO	x	0.308	0.283	0.274	0.303
	y	0.311	0.284	0.301	0.333
Bin YA	x	0.308	0.311	0.290	0.283
	y	0.311	0.293	0.270	0.284

Tolerance: ±0.01

Warm White	Color Limits (Chromaticity Coordinates)				
Bin MM	x	0.471	0.460	0.473	0.486
	y	0.451	0.430	0.432	0.455
Bin M1	x	0.460	0.453	0.467	0.473
	y	0.430	0.416	0.419	0.432
Bin M0	x	0.453	0.444	0.459	0.467
	y	0.416	0.399	0.403	0.419
Bin MA	x	0.459	0.444	0.436	0.451
	y	0.403	0.399	0.384	0.389
Bin NM	x	0.454	0.444	0.460	0.453
	y	0.446	0.426	0.430	0.416
Bin N1	x	0.444	0.438	0.453	0.436
	y	0.426	0.412	0.416	0.384
Bin N0	x	0.438	0.429	0.444	0.460
	y	0.412	0.394	0.399	0.430
Bin NA	x	0.444	0.429	0.422	0.471
	y	0.399	0.394	0.379	0.451
Bin PM	x	0.438	0.430	0.444	0.454
	y	0.440	0.421	0.426	0.446
Bin P1	x	0.430	0.424	0.438	0.444
	y	0.421	0.407	0.412	0.426
Bin P0	x	0.424	0.416	0.429	0.438
	y	0.407	0.389	0.394	0.412
Bin PA	x	0.429	0.416	0.410	0.422
	y	0.394	0.389	0.374	0.379
Bin QM	x	0.421	0.414	0.430	0.438
	y	0.433	0.414	0.421	0.440
Bin Q1	x	0.414	0.409	0.424	0.430
	y	0.414	0.400	0.407	0.421
Bin Q0	x	0.409	0.402	0.416	0.424
	y	0.400	0.382	0.389	0.407
Bin QA	x	0.416	0.402	0.396	0.410
	y	0.389	0.382	0.367	0.374

Tolerance: ±0.01

<b>Neutral White</b>	<b>Color Limits (Chromaticity Coordinates)</b>				
Bin RM	x	0.421	0.414	0.397	0.402
	y	0.433	0.414	0.406	0.423
Bin R1	x	0.414	0.409	0.392	0.397
	y	0.414	0.400	0.391	0.406
Bin R0	x	0.392	0.387	0.402	0.409
	y	0.391	0.374	0.382	0.400
Bin RA	x	0.387	0.383	0.396	0.402
	y	0.374	0.360	0.367	0.382
Bin SM	x	0.402	0.397	0.382	0.386
	y	0.423	0.406	0.397	0.413
Bin S1	x	0.397	0.392	0.378	0.382
	y	0.406	0.391	0.382	0.397
Bin S0	x	0.392	0.387	0.374	0.378
	y	0.391	0.374	0.366	0.382
Bin SA	x	0.387	0.383	0.370	0.374
	y	0.374	0.360	0.351	0.366
Bin TM	x	0.386	0.382	0.365	0.367
	y	0.413	0.397	0.386	0.400
Bin TN	x	0.382	0.378	0.362	0.365
	y	0.397	0.382	0.372	0.386
Bin T0	x	0.378	0.374	0.360	0.362
	y	0.382	0.366	0.357	0.372
Bin TP	x	0.374	0.370	0.357	0.360
	y	0.366	0.351	0.342	0.357

Tolerance: ±0.01

<b>Dominant Wavelength (nm) at 350 mA</b>			
<b>Color</b>	<b>Bin ID</b>	<b>Min.</b>	<b>Max.</b>
Red	—	620.0	635.0
Red Orange	—	610.0	620.0
Amber	B	587.0	589.5
	C	589.5	592.0
	D	592.0	594.5
	E	594.5	597.0
Blue	A	460.0	465.0
	B	465.0	470.0
	C	470.0	475.0
	D	475.0	480.0
Green	A	515.0	520.0
	B	520.0	525.0
	C	525.0	530.0
	D	530.0	535.0

Tolerance: ± 1 nm

<b>Peak Wavelength (nm) at 350 mA</b>			
<b>Color</b>	<b>Bin ID</b>	<b>Min.</b>	<b>Max.</b>
Royal Blue	C	440.0	445.0
	D	445.0	450.0
	E	450.0	455.0
	F	455.0	460.0

Tolerance: ±2 nm

#### Packaging Option [x4]

<b>Selection</b>	<b>Option</b>
1	Tape and Reel

#### Example

ASMT-JY11-NST01

ASMT-JY11-Nxxxx – Warm White, InGaN,  
Electrically isolated Heat Sink

X<sub>1</sub> = S – Minimum Flux Bin S

X<sub>2</sub> = T – Maximum Flux Bin T

X<sub>3</sub> = 0 – Full Distribution

X<sub>4</sub> = 1 – Tape and Reel Option

## Tape and Reel – Option 1





Figure 28. Carrier Tape Dimensions



Notes:

1. Empty component pockets sealed with top cover tape.
2. 250 or 500 pieces per reel.
3. Drawing not to scale.
4. All dimensions are in millimeters.

Figure 29. Reel dimensions




Figure 30. Reeling Orientation

**DISCLAIMER:** Avago's products and software are not specifically designed, manufactured or authorized for sale as parts, components or assemblies for the planning, construction, maintenance or direct operation of a nuclear facility or for use in medical devices or applications. Customer is solely responsible, and waives all rights to make claims against avago or its suppliers, for all loss, damage, expense or liability in connection with such use.

For product information and a complete list of distributors, please go to our web site: [www.avagotech.com](http://www.avagotech.com)

Avago, Avago Technologies, and the A logo are trademarks of Avago Technologies in the United States and other countries.  
Data subject to change. Copyright © 2005-2009 Avago Technologies. All rights reserved.  
AV02-1770EN - July 10, 2009

**AVAGO**  
TECHNOLOGIES