



Main

Product or component type	Starter
Range of product	Type S

Complementary

Control circuit	Separate control circuit
Control type	Without
NEMA degree of protection	Not rated (open device)
Auxiliary contact composition	Without
Maximum Horse Power Rating	25 Hp 200 V AC, 3 phase 30 Hp 230 V AC, 3 phase 50 Hp 380 V AC, 3 phases 50 hp 460/575 V AC, 3 phase
Poles description	3P
Maximum operating voltage	600 V AC
NEMA size	3
[Uc] control circuit voltage	120 V AC 60 Hz 110 V AC 50 Hz
Local signalling	Without pilot light
Motor starter type	2 speed
Electrical connection	Lugs
Thermal overload type	Melting alloy
Number of thermal units required	6
Asynchronous motor control profile	Constant/variable torque
Maximum operating current	90 A

Environment

Product certifications	UL listed file E78351 CCN NLDX CSA LR60905 class 3211 04
------------------------	---

Ordering and shipping details

Category	21302 - 8810,11,12 S
Discount Schedule	CP1
GTIN	00785901890508
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Not compliant
China RoHS Regulation	 China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------