

Product Discontinuation Notices

Programmable Relays

Issue Date
January 5, 2022

No. 2022006CE

Discontinuation Notice of Programmable Relays Model ZEN series.

Product Discontinuation

Programmable Relays

Model ZEN series



Recommended Replacement

Programmable controller

Model CP2E series



[Final order entry date]

The end of March 2024

[Date of The Last Shipping]

The end of June 2024

[Caution on recommended replacement]

ZEN series are no maintenance.

Programmable relay ZEN series will be discontinued to manufacture and integrated to Programmable controller CP2E series.

Many specifications of ZEN are different from CP2E. So, please confirm the detail in manual and replace system.

[Difference from discontinued product]

Recommended replacement Model	Body Color	Dimensions	Wire connection	Mounting Dimensions	Characteristics	Operation ratings	Operation methods
CP2E series	--	--	--	--	--	--	--

** : Compatible

* : The change is a little/Almost compatible



-- : Not compatible

- : No corresponding specification








[Product Discontinuation and recommended replacement]

Product discontinuation	Recommended replacement
ZEN-10C1AR-A-V2	CP2E-N14DR-A
ZEN-10C1DR-D-V2	CP2E-N14DR-D
ZEN-10C1DT-D-V2	CP2E-N14DT-D
ZEN-10C2AR-A-V2	CP2E-N14DR-A
ZEN-10C2DR-D-V2	CP2E-N14DR-D
ZEN-10C2DT-D-V2	CP2E-N14DT-D
ZEN-10C3AR-A-V2	CP2E-N14DR-A
ZEN-10C3DR-D-V2	CP2E-N14DR-D
ZEN-10C4AR-A-V2	CP2E-N14DR-A
ZEN-10C4DR-D-V2	CP2E-N14DR-D
ZEN-20C1AR-A-V2	CP2E-N20DR-A
ZEN-20C1DR-D-V2	CP2E-N20DR-D
ZEN-20C1DT-D-V2	CP2E-N20DT-D
ZEN-20C2AR-A-V2	CP2E-N20DR-A
ZEN-20C2DR-D-V2	CP2E-N20DR-D
ZEN-20C2DT-D-V2	CP2E-N20DT-D
ZEN-20C3AR-A-V2	CP2E-N20DR-A
ZEN-20C3DR-D-V2	CP2E-N20DR-D
ZEN-8E1AR	No recommended replacement
ZEN-8E1DR	No recommended replacement
ZEN-8E1DT	No recommended replacement













[Body color]

Product discontinuation Model ZEN series	Recommendable replacement Model CP2E series
<p>Ivory</p> 	<p>Black</p> 

[Dimensions]

Product discontinuation Model ZEN series	Recommendable replacement Model CP2E series
<p>CPU Units with 10 I/O points</p>  <p>CPU Units with 20 I/O points</p>  <p>Expansion I/O Units</p>  <p style="text-align: center;">Unit : mm</p>	<p>All dimensions (H × D × W) are changed from ZEN.</p> <p>CPU Units with 14/20 I/O points</p>  <p>CPU Units with 30 I/O points</p>  <p>CPU Units with 40 I/O points</p>  <p>CPU Units with 60 I/O points</p>  <p style="text-align: center;">Unit : mm</p>

[Wire connection]

<p align="center">Product discontinuation Model ZEN series</p>	<p align="center">Recommendable replacement Model CP2E series</p>
<p>Terminal block : European type</p> <p>Wiring Diagrams Example: ZEN-10C1AR-A-V2 - Input wiring diagram 100 to 240 VAC, 50/60 Hz</p>  <p>CPU Unit with 10 I/O points ZEN-8E1AR Expansion I/O Unit (AC input type)</p> <p>100 to 240 VAC, 50/60 Hz</p>  <p>CPU Unit with 10 I/O points Expansion I/O Unit ZEN-8E1DR (DC inputs and relay outputs) Expansion I/O Unit ZEN-8E1DT (DC inputs and transistor outputs)</p> <p>- Output wiring diagram CPU Unit with 10 I/O points</p> 	<p>Terminal block : M3 screw type.</p> <p>Wiring Diagrams Example : CPU Units with 14/20 I/O points - Input wiring diagram</p>  <p>24V DC C10 0</p> <p>DC Power Supply N14DC0-D</p> <p>* : 0ch08 to 11bit are NC with 14 I/O points.</p> <p>- Output wiring diagram Relay output</p>  <p>100CH</p> <p>Transistor output (Sink type)</p>  <p>100CH</p> <p>Transistor output (Source type)</p>  <p>100CH</p> <p>* : 1000ch06 to 07bit are NC with 14 I/O points.</p>
<p>Example: ZEN-10C1D[]-D-V2 - Input wiring diagram Connecting a negative Common</p>  <p>12 to 24 VDC</p> <p>CPU Unit with 10 I/O points CPU Unit with 10 I/O points</p> <p>12 to 24 VDC</p> <p>CPU Unit with 10 I/O Points Expansion I/O Unit ZEN-8E1DR (with DC power input and relay outputs) Expansion I/O Unit ZEN-8E1DT (with DC power input and transistor outputs)</p> <p>- Output wiring diagram Relay type CPU Unit with 10 I/O points</p>  <p>Transistor type CPU Unit with 10 I/O points</p>  <p>Q0 to Q3</p>	<p>Transistor output (Sink type)</p>  <p>100CH</p> <p>Transistor output (Source type)</p>  <p>100CH</p> <p>* : 1000ch06 to 07bit are NC with 14 I/O points.</p>

[Characteristics]

Item	Product discontinuation Model ZEN series	Recommendable replacement Model CP2E series
Power Supply voltage	AC type : 100 to 240 VAC DC type : 12 to 24 VDC	AC type : 100 to 240 VAC DC type : 24 VDC
Ambient operating temperature	LCD type : 0 to 55°C LED type : -25 to 55°C	-20 to 60°C
Ambient storage temperature	LCD type : -20 to 75°C LED type : -40 to 75°C	-20 to 75°C
Degree of protection	IP20 (Mounted in a panel)	IP20 (Mounted in a panel)
LCD display, Operation button	LCD : 12 characters × 4 lines Button : 8	None
Memory Cassette	ZEN-ME01 Used to save and copy programs	None
Calendar / Time	Accuracy : +/-15 s/month (at 25°C) (Only provide for LCD type)	Accuracy : +/-120 s/month (at 25°C)
Battery	ZEN-BAT01	CP2E-BAT02
Maximum number of I/O points	44 points	180 points
Program capacity	96 lines (up to 3 inputs and 1 output per line)	10 k steps (CP2E-N)
Data backup for power interruptions	- Internal holding bit status, holding timer/counter present values, calendar and clock Super Capacitor : 2 days (at 25°C) Battery (Option)	- Holding area data, DM Area data, Counter completion flags, Counter present values and Auxiliary area data non-volatile memory (Battery less) - Clock Battery (Option)
Programming device	ZEN-SOFT01-V1	CX-Programmer Ver.9.72 or higher
Input	AC inputs	100 to 240 VAC, 50/60 Hz
	DC inputs	12 to 24 VDC
	Analog inputs	0 – 10 V
Output	Relay outputs	250 VAC/8 A, 24 VDC/5 A
	Transistor outputs	24 VDC/0.5 A

* : Only main Specification and characteristics are described.
For details, refer to the datasheet or manual of each product.

Specifications and prices in this product news are as of the issue date and are subject to change without notice.
Only main changes in specifications are described in this document. Please be sure to read the relevant catalogs, datasheets, product specifications, instructions, and manuals for precautions and necessary information when using products.