

# Product data sheet

Specifications



Monolithic pre wired tower light,  
Harmony XVC, plastic, red, 60mm,  
base mounting, steady or flashing,  
buzzer, IP54, 24V AC DC

XVC6B15SK

Product availability: Stock - Normally stocked in distribution facility

## Main

Range Of Product	Harmony XVC6
Product Or Component Type	Complete pre-wired monolithic tower light
Beacon Or Indicator Bank Unit Type	1 illuminated unit
Sound Signalling	Buzzer
Mounting Diameter	2.36 in (60 mm)
Component Name	XVC
Light Source	LED steady or flashing red
[Us] Rated Supply Voltage	24 V
Supply Circuit Type	AC/DC
Noise Level	70...85 dB continuous or intermittent tone)1 m

## Complementary

Material	Polycarbonate: illuminated unit ABS (acrylonitrile butadiene-styrene): base unit PBT + ABS (UL94HB): top cover
Product Mounting	On base
Cable Cross Section	0.00 in <sup>2</sup> (0.33 mm <sup>2</sup> )
Awg Gauge	AWG 22
Cable Length	33.46 in (850 mm)
Marking	CE
[Uimp] Rated Impulse Withstand Voltage	0.8 kV
Current Consumption	65 mA
Fundamental Frequency	2.23 kHz
Flashing Frequency	1 Hz
Net Weight	0.44 lb(US) (0.2 kg)
Height	4.76 in (120.8 mm)

## Environment

Standards	EN/IEC 61000-6-2 EN/IEC 61000-6-4 EN/IEC 61000-6-3
-----------	--

<b>Product Certifications</b>	UL
<b>Protective Treatment</b>	TC
<b>Ambient Air Temperature For Storage</b>	-31...158 °F (-35...70 °C)
<b>Ambient Air Temperature For Operation</b>	14...122 °F (-10...50 °C)
<b>Electrical Shock Protection Class</b>	Class II EN/IEC 61140
<b>Ip Degree Of Protection</b>	IP54 flat surface installation EN/IEC 60529

## Ordering and shipping details

<b>Category</b>	US100XV22617
<b>Discount Schedule</b>	00XV
<b>Gtin</b>	3606480032691
<b>Returnability</b>	Yes
<b>Country Of Origin</b>	ID

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	3.40 in (8.64 cm)
<b>Package 1 Width</b>	3.40 in (8.64 cm)
<b>Package 1 Length</b>	20.00 in (50.8 cm)
<b>Package 1 Weight</b>	0.97 lb(US) (0.44 kg)
<b>Unit Type Of Package 2</b>	S04
<b>Number Of Units In Package 2</b>	12
<b>Package 2 Height</b>	11.81 in (30 cm)
<b>Package 2 Width</b>	15.75 in (40 cm)
<b>Package 2 Length</b>	23.62 in (60 cm)
<b>Package 2 Weight</b>	14.15 lb(US) (6.42 kg)

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

**Eu Rohs Directive** [Pro-active compliance \(Product out of EU RoHS legal scope\)](#)

**China Rohs Regulation** [China RoHS declaration](#)

**Environmental Disclosure** [Product Environmental Profile](#)

**Circularity Profile** [End of Life Information](#)


**California Proposition 65** **WARNING:** This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

Dimensions Drawings

Pre-assembled and Pre-wired Tower Light

Dimensions

Below drawing shows the maximum configuration of the product. Select the number of stages according to the product characteristics in order to get **b** dimension.



No. of illuminated units	b (mm)	b (in.)
1 stage	120.8	4.76
2 stages	160.8	6.33
3 stages	200.8	7.90
4 stages	240.8	9.48
5 stages	280.8	11.06

Mounting and Clearance

**Pre-assembled and Pre-wired Tower Light**

---

**Mounting on Horizontal Support (Direct or with Fixing Plate)**

Panel cut-out

