

TMM55E-PMH045

TMM55

INCLINATION SENSORS

SICK
Sensor Intelligence.



Illustration may differ

Ordering information

| Type | Part no. |
|---------------|----------|
| TMM55E-PMH045 | 1073781 |

Other models and accessories → www.sick.com/TMM55



Detailed technical data

Performance

| | |
|--|--------------------------|
| Number of axis | 2 |
| Measuring range | ± 45° |
| Resolution | 0.05° |
| Static measurement accuracy | ± 0.3° |
| Compensated cross-sensitivity (2-dimensional) | Typ. ± 0.9°, max. ± 1.8° |
| Temperature coefficient (zero point) | Max. ± 0.009°/K |
| Limit frequency | 18 Hz |
| Sampling rate | 1.95 kHz |

Interfaces

| | |
|--------------------------------|------------------|
| Communication interface | Analog / Current |
| Current output | 4 mA ... 20 mA |
| Load resistance | ≤ 930 Ω |
| Initialization time | 75 ms |

Electrical data

| | |
|--|---|
| Connection type | Cable, 5-wire, with male connector, M12, 5-pin, 0.2 m |
| Supply voltage | 11 V DC ... 30 V DC |
| Current consumption | 15 ... 45 mA |
| Reverse polarity protection | ✓ |
| Short-circuit protection of the outputs | ✓ |
| MTTFd: mean time to dangerous failure | 378 years (EN ISO 13849-1) ¹⁾ |

¹⁾ This product is a standard product and does not constitute a safety component as defined in the Machinery Directive. Calculation based on nominal load of components, average ambient temperature 40 °C, frequency of use 8760 h/a. All electronic failures are considered hazardous. For more information, see document no. 8015532.

Mechanical data

| | |
|-------------------------|-----------------------|
| Dimensions | 65 mm x 35 mm x 20 mm |
| Weight | 55 g (with cable) |
| Housing material | Plastic (ABS) |
| Material, cable | PUR |


Ambient data

| | |
|------------------------------------|--|
| EMC | EN 61326-1, EN ISO 14982, EN ISO 13309 |
| Enclosure rating | IP65 IP67 |
| Operating temperature range | -40 °C ... +80 °C |
| Storage temperature range | -40 °C ... +85 °C |
| Resistance to shocks | 100 g, 6 ms (according to EN 60068-2-27) |
| Resistance to vibration | 10 g, 10 Hz ... 2,000 Hz (EN 60068-2-6) |


Classifications

| | |
|-----------------------|----------|
| eCl@ss 5.0 | 27270790 |
| eCl@ss 5.1.4 | 27270790 |
| eCl@ss 6.0 | 27270790 |
| eCl@ss 6.2 | 27270790 |
| eCl@ss 7.0 | 27270790 |
| eCl@ss 8.0 | 27270790 |
| eCl@ss 8.1 | 27270790 |
| eCl@ss 9.0 | 27270790 |
| eCl@ss 10.0 | 27271101 |
| eCl@ss 11.0 | 27271101 |
| eCl@ss 12.0 | 27271101 |
| ETIM 5.0 | EC001852 |
| ETIM 6.0 | EC001852 |
| ETIM 7.0 | EC001852 |
| ETIM 8.0 | EC001852 |
| UNSPSC 16.0901 | 41111613 |

Dimensional drawing (Dimensions in mm (inch))




PIN assignment




| PIN Male connector M12, 5-pin | Wire colors (cable connection) Cable connection | Signal | Function |
|----------------------------------|--|-------------|---|
| 1 | Brown | VDC | Supply voltage |
| 2 | White | Y-OUT | Sensorsignal y-axis |
| 3 | Blue | GND | 0V (GND) |
| 4 | Black | X-OUT | Sensorsignal x-axis |
| 5 | Green/yellow | Signal- GND | Signal GND (internally connected to GND) |


Diagrams



Recommended accessories

Other models and accessories → www.sick.com/TMM55

| | Brief description | Type | Part no. |
|---|--|------------------------|----------|
| Plug connectors and cables | | | |
|  | Head A: female connector, M12, 5-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, Power, PUR, halogen-free, shielded, 1.5 m | DOL-1205- W1M5ACSCO | 6049455 |

| | Brief description | Type | Part no. |
|---|---|--------------------|----------|
|  | Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, shielded, 1.5 m | YF2A25-015UB6XLEAX | 2095833 |
| | Head A: female connector, M12, 5-pin, straight, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, shielded, 3 m | YF2A25-030UB6XLEAX | 2095834 |
|  | Head A: female connector, M12, 5-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, shielded, 3 m | YG2A25-030UB6XLEAX | 2095791 |
| | Head A: female connector, M12, 5-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, shielded, 5 m | YG2A25-050UB6XLEAX | 2095792 |
| | Head A: female connector, M12, 5-pin, angled, A-coded Head B: Flying leads Cable: Sensor/actuator cable, PUR, halogen-free, shielded, 10 m | YG2A25-100UB6XLEAX | 2095793 |
|  | Head A: female connector, M12, 5-pin, straight Cable: unshielded | DOS-1205-G | 6009719 |
|  | Head A: male connector, M12, 5-pin, straight Cable: unshielded For field bus technology | STE-1205-G | 6022083 |

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com