


COAXIAL ATTENUATORS

BNC

1 - 2 WATTS

| Part Number | Frequency range (GHz) | ATTENUATION (dB) | | | V.S.W.R. | | Power (W) | | Fig. |
|-------------|-----------------------|------------------|-----------|-------|----------|--------|-----------|------|------|
| | | Nominal | DEVIATION | | DC - 2 | 2 - 3 | avg. | peak | |
| | | | DC - 2 | 2 - 3 | | | | | |
| R412400000 | DC - 2 | 0 | + 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412401000 | | 1 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412402000 | | 2 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412403000 | | 3 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412404000 | | 4 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412405000 | | 5 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412406000 | | 6 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412407000 | | 7 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412408000 | | 8 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412409000 | | 9 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412410000 | | 10 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412411000 | | 11 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412412000 | | 12 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412413000 | | 13 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412414000 | | 14 | ± 0.35 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412415000 | | 15 | + 0.40 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412420000 | | 20 | + 0.45 | | ≤ 1.20 | | 2 | 100 | 1 |
| R412430000 | | 30 | ± 0.80 | | ≤ 1.20 | | 2 | 100 | 2 |
| R412440000 | | 40 | ± 0.80 | | ≤ 1.20 | | 2 | 100 | 2 |
| R412450000 | | 50 | ± 1.00 | | ≤ 1.25 | | 2 | 100 | 2 |
| R412400124 | DC - 3 | 0 | + 0.3 | + 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412401124 | | 1 | ± 0.3 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412402124 | | 2 | ± 0.3 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412403124 | | 3 | ± 0.3 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412404124 | | 4 | ± 0.3 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412405124 | | 5 | ± 0.3 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412406124 | | 6 | ± 0.3 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412407124 | | 7 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412408124 | | 8 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412409124 | | 9 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412410124 | | 10 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412411124 | | 11 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412412124 | | 12 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412413124 | | 13 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412414124 | | 14 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412415124 | | 15 | ± 0.5 | ± 0.5 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412416124 | | 16 | ± 0.7 | ± 0.7 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412417124 | | 17 | ± 0.7 | ± 0.7 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412418124 | | 18 | ± 1.0 | ± 1.0 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412419124 | | 19 | ± 1.0 | ± 1.0 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |
| R412420124 | | 20 | ± 1.0 | ± 1.0 | ≤ 1.20 | ≤ 1.30 | 1 | 100 | 3 |



| Figure | A inch (mm) | B inch (mm) | Weight (g) |
|--------|--------------|-------------|------------|
| 1 | 1.83" (46.5) | .51" (13) | 30 |
| 2 | 2.25" (57.1) | | 40 |
| 3 | 1.26" (32) | | 17 |

