



VT-60012 12W BACKLIT SURFACE MOUNTED
PANEL 3000K SQ



FEATURES

- Strong and sturdy body Backlit Mini Panels
- High quality power driver ensures reliable lifetime
- Designed with high efficiency LED SMD chips.
- No Lead or Mercury content hence Environment friendly
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

TECHNICAL INFORMATION

Dimmable:	No
Color Temperature:	3000K
Model:	VT-60012-SQ
Watts:	12
Lumens:	1200
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Color for Web:	Warm White
Dimension:	167.3x167.3x30.7mm
Operation Temperature:	-20°C to +45°C
On/Off Cycles:	>15000
LED Chip Type:	SMD
Input Current:	71mA
CRI:	>80
Energy Rating Label:	F (2021)
IP Rating:	IP20
Long Life:	20,000 Hours
Energy Saving:	85 Energy



IP20
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	10495
Model:	VT-60012-SQ
EAN:	3800170208827
Commodity Code:	94051140

PACKAGING

Gross Weight (Kgs):	0.23
Unit CBM:	0.001305
Dimension:	167.3x167.3x30.7mm

MASTER BOX PACKAGING

Box Qty:	60
Qty Per Pallet:	1200
Length (Box) mm:	175
Width (Box) mm:	35
Height (Box) mm:	175