



Product data sheet

Power tools for trade & industry

Line Laser

GLL 2-15 G



Durability and ease of use. Green laser lines

The most important data

Working range	up to 15 m
Accuracy	$\pm 0.3 \text{ mm/m}^*$ (* plus use-dependent deviation)
Self-levelling range	$\pm 4^\circ$

Part Number 0 601 063 W00

[> More product information](#)

Technical data

Technical data

Operating temperature	-10 – 50 °C
Storage temperature	-20 – 70 °C
Working range	up to 15 m
Accuracy	$\pm 0.3 \text{ mm/m}^*$ (*plus use-dependent deviation)
Self-levelling range	$\pm 4^\circ$
Levelling time	4 s
Dust and splash protection	IP 64
Power supply	4 x 1.5 V LR6 (AA)
Tripod thread	1/4"
Weight, approx.	0.57 kg
Colour of laser line	green
Projection	2 lines

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Durable design, featuring a rubberised housing with recessed glasses and dust and splash water protection IP 64 to withstand tough environments
- ON/OFF switch and one-button keypad make for ease of use
- Green laser for enhanced horizontal and vertical line visibility

**PROTECTED TOOLS**
Impact | Water | Dust