

Product data sheet

Specifications



TeSys D - suppressor module - RC circuit - 24...48 V AC

LA4DA1E

Product availability : Stock - Normally stocked in distribution facility

Main

Range	TeSys
Device short name	LA4D
Product or Component Type	Suppressor module
Product compatibility	3P LC1D80...D150

Complementary

Mounting Mode	By screws
Suppressor technology	RC circuit
[Uc] control circuit voltage	24...48 V AC 50/60 Hz
Maximum peak voltage	3 Uc

Environment

Ambient Air Temperature for Operation	-13...131 °F (-25...55 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	22341-CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	3389110233001
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.10 in (2.8 cm)
Package 1 Width	1.65 in (4.2 cm)
Package 1 Length	2.01 in (5.1 cm)

Package 1 Weight	0.56 oz (16.0 g)
Unit Type of Package 2	S01
Number of Units in Package 2	78
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	3.19 lb(US) (1.449 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)