

Glass Passivated 3 Phase Bridge Rectifier

multicomp PRO



Features

- Low forward voltage drop
- High current capability
- High reliability
- High surge current capability
- Ideal for printed circuit boards

Mechanical Data

Case	: Epoxy case with heat sink laterally mounted in the bridge encapsulation
Terminals	: Plated leads solderable per MIL-STD-202, Method 208
Polarity	: As Marked on Body
Weight	: 21 grams(approx.)
Mounting Position	: Bolt down on heatsink with silicone thermal compound between bridge and mounting surface for maximum heat transfer efficiency.
Mounting Torque	: 2 N.m

Maximum Ratings And Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%

Voltage Ratings							Unit
Characteristics	Symbol	SMT5008GW	SMT5010GW	SMT5012GW	SMT5014GW	SMT5016GW	
Peak Repetitive Voltage	VRRM						V
Working Peak Reverse Voltage	VRWM	800	1000	1200	1400	1600	
DC Blocking Voltage	VR						
Peak Non-Repetitive Reverse Voltage	VRSM	900	1100	1300	1500	1700	
RMS Reverse Voltage	VR(RMS)	560	700	840	980	1120	
Forward Conduction							
Characteristics	Symbol	SMT50GW Series					Unit
Maximum Average Forward Rectified Current @Tc = 55°C	Io	50					A
Peak Forward Surge Current t=8.3ms at 60Hz	IFSM	400					
I²t Rating for fusing	I²t	840					A²S
Maximum Forward Voltage drop per element at 25A Peak	VF	1.1					V
Reverse peak current VR=VRRM@TJ=25°C VR=VRRM@TJ=150°C	IR	5 3					µA mA
RMS isolation Voltage from case to lead	VISO	2500					V
Thermal Characteristics							
Operating Temperature Range	TJ	-40 to +150					°C
Storage Temperature Range	TSTG	-40 to +125					

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO

Glass Passivated 3 Phase Bridge Rectifier

Rating and Characteristic Curves

FIG.1-MAXIMUM FORWARD SURGE CURRENT




FIG.2- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG.3-TYPICAL FORWARD CHARACTERISTICS





FIG.4-TYPICAL REVERSE CHARACTERISTICS




Glass Passivated 3 Phase Bridge Rectifier

multicomp PRO

Dimension

SMTGW



Part Number Table

Description	Part Number
Three Phase Bridge 50A 800V SMTGW Package	SMT5008GW
Three Phase Bridge 50A 1000V SMTGW Package	SMT5010GW
Three Phase Bridge 50A 1200V SMTGW Package	SMT5012GW
Three Phase Bridge 50A 1400V SMTGW Package	SMT5014GW
Three Phase Bridge 50A 1600V SMTGW Package	SMT5016GW

Dimensions : Inches (Millimetres)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp PRO