

FIREXO 6L ALL FIRES EXTINGUISHER

PRODUCT	FIREXO 6L ALL FIRES
MODEL/PRODUCT NO.	809-765-347-876
CAPACITY	6 LITRES
OVERALL PRODUCT HEIGHT	520 mm
CYLINDER HEIGHT	430 mm
CYLINDER DIAMETER	162 mm
CYLINDER MATERIAL	STEEL
PRESSURISING GAS	NITROGEN
TEST PRESSURE	30 BAR
WORKING PRESSURE	12 BAR
WEIGHT (FULL)	10.67 KG
WEIGHT (EMPTY)	3.65 KG
SPRAY RANGE	1-4 m
DISCHARGE TIME	25-35 seconds
TEMPERATURE RANGE	-15 °C / +60 °C
WARRANTY	5 YEARS
FIRE RATINGS	34A/113B/C/D/ELECTRICAL/75F/LITHIUM-ION



METHOD OF USE

In the event of a fire hold extinguisher upright, pull out safety pin, point hose at base of fire, squeeze handle and sweep side to side.

Discharge entire contents onto the fire from a 1m-3m distance.

Store upright and away from direct sunlight or heat source.

Protect from frost.

Replace or recharge after use.

Tested on electrical equipment fires to 35kV.