

FIREXO 2L ALL FIRES EXTINGUISHER STAINLESS STEEL

PRODUCT	FIREXO 2L STAINLESS STEEL ALL FIRES
MODEL/PRODUCT NO.	809-765-347-066
CAPACITY	2 LITRES
OVERALL PRODUCT HEIGHT	430 mm
CYLINDER HEIGHT	335 mm
CYLINDER DIAMETER	110 mm
CYLINDER MATERIAL	STAINLESS STEEL
PRESSURISING GAS	NITROGEN
TEST PRESSURE	30 BAR
WORKING PRESSURE	12 BAR
WEIGHT (FULL)	3.52 KG
WEIGHT (EMPTY)	1.18 KG
SPRAY RANGE	1-3 m
DISCHARGE TIME	15-20 SECONDS
TEMPERATURE RANGE	-15 °C / +60 °C
WARRANTY	5 YEARS
FIRE RATINGS	13A/34B/C/D/ELECTRICAL/25F/LITHIUM-ION



METHOD OF USE

In the event of a fire hold extinguisher upright, pull out safety pin, aim at base of fire, squeeze handle and sweep side to side.

Discharge entire contents onto the fire from a 1m-3m distance.

Store upright and away from direct sunlight or heat source.

Protect from frost.

Replace or recharge after use.

Tested on electrical equipment fires to 35kV.