

RefLED Superia Retro MR16 DIMMABLE
RefLED Superia Retro MR16 V2 345LM DIM 830 36 SL
0029215



Product features

- Premium performance professional LED MR16 range with the same look and feel of traditional halogen MR16 lamp
- Recreates backlight effect similar to halogen dichroic lamps.
- Full glass design - means no colours clashing between lamp and fixture
- Very long lifetime of up to 25,000 hours
- Switching cycles: >100,000
- Colour rendering: CRI80
- Lamp voltage: 12V AC/DC
- Dimmable on approved dimmers
- Works with magnetic and compatible electronic transformers
- Warranty: 5 Years



PRODUCT OVERVIEW

Product name	RefLED Superia Retro MR16 V2 345LM DIM 830 36 SL
Technology	LED
Watt (Rated) (W)	4.4
Fixture rating	Open
General application	Education, Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
ETIM Class	EC001959
E-number FI	4741095
Warranty	5 years
Useful luminous flux (Fuse)	345
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Colour Consistency (SDCM)	6
Beam Angle (°)	36
Photobiological Risk Group	RG1
Power consumption (W)	4.4
Wattage (W)	4.4
Dimmable	Yes
Average life (Nominal) (h)	25000
Product EAN number	5410288292151

DATA TABLE

General data

Product name	RefLED Superia Retro MR16 V2 345LM DIM 830 36 SL
Technology	LED
Watt (Rated) (W)	4.4
Fixture rating	Open

RefLED Superia Retro MR16 DIMMABLE

RefLED Superia Retro MR16 V2 345LM DIM 830 36 SL

0029215

General application	Education, Hospitality, Museums & Galleries, Office, Residential & Consumer, Retail
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001959
E-number FI	4741095
Warranty	5 years

Optical data

Useful luminous flux (Fuse)	345
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM6
Colour Consistency (SDCM)	6
Luminous Intensity (cd)	800
Beam Angle (°)	36
Photobiological Risk Group	RG1
Lumen maintenance at end of nominal life (%)	70

Electrical data

Power consumption (W)	4.4
Wattage (W)	4.4
Equivalent watt (W)	35
Primary Supply/Product voltage - min (V)	12
Primary Supply/Product voltage - max (V)	12
Control gear required	Yes
No. Of switching cycles before premature failures	>50000
Dimmable	Yes
Inrush Current (A)	6.5
Inrush Duration (µs)	500
Lamp Energy Label (class)	F

Lifetime data

Lifespan L70 B50	25000
Average life (Nominal) (h)	25000
Average life (Rated) (h)	25000

Physical data

Nominal Product Length (mm)	44
Nominal Product Diameter (mm)	50
Weight (kg)	0.03

Packaging

Product EAN number	5410288292151
Packaging single length / height (cm)	6.1


RefLED Superia Retro MR16 DIMMABLE
RefLED Superia Retro MR16 V2 345LM DIM 830 36 SL
0029215

Packaging single width (cm)	5.1
Packaging single depth (cm)	8.2
DUN14 (inner)	25410288292155
Units per inner package	6
Packaging inner length / height (cm)	16.4
Packaging inner width (cm)	13.2
Packaging inner depth (cm)	9.3
DUN14 (outer)	15410288292158
Units per outer package	48
Packaging outer length / height (cm)	34.6
Packaging outer width (cm)	28.2
Packaging outer depth (cm)	20.8


Safety data

Optimal operating condition (°C)	-20-40
Breakage cleaning instructions	Not applicable
Special purpose lamp	No
Dry applications use only	Yes
Suitable for household illumination	Yes
Safety message	Suitable for approved transf./dimmers

PHOTOMETRY



TECHNICAL DRAWINGS




RefLED Superia Retro MR16 DIMMABLE
RefLED Superia Retro MR16 V2 345LM DIM 830 36 SL
0029215



SYLVANIA

0029215



5
kWh/1000h




2019/2015

RefLED Superia Retro MR16 DIMMABLE
RefLED Superia Retro MR16 V2 345LM DIM 830 36 SL
0029215



0029215



5
kWh/1000h

