
Product data sheet
Characteristics

VW3A3407
encoder interface card with push-pull outputs - 24 V DC



Main

Range of product	Altivar
Product or component type	Encoder interface card
Range compatibility	Altivar 61Q Altivar 71Q Altivar 71 Altivar 61 Altivar Lift
Discrete output type	Push-pull
[Us] rated supply voltage	24 V DC 20…30 V)
Number of pulses per revolution	10000 ATV71H.....383 5000 all ATV61 drives 5000 ATV71H...M3 5000 ATV71H...M3X 5000 ATV71H...N4

Complementary

Maximum supply current	0.175 A
Protection type	Overload protection Short-circuit protection
Maximum cable distance between devices	1640.42 ft (500 m)
Maximum operating frequency	300 kHz
Input signal	A B Compliment of A Compliment of B/AB/A
Input impedance	1000 Ohm
Voltage state 0 guaranteed	<= 1.5 V
Voltage state 1 guaranteed	> 11.5...< 25 V
Electrical connection	Terminal 0.2 mm² AWG 24) <1640.42 ft (500 m), encoder, 100 mA 14 V

Ordering and shipping details

Category	22135 - ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	00785901526919
Returnability	Yes
Country of origin	ID

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty	18 months