Product data sheet

Specifications



dual function relay, Harmony Timer Relays, 5A, 2CO, 0.02s... 300h, asymmetrical flashing, 24...240V AC DC

RE48ACV12MW

Product availability: Stock - Normally stocked in distribution facility

Main

Range Of Product	Harmony Timer Relays
Product Or Component Type	Dual function relay
Electrical Connection	Plug-in sub-base 11
Width	1.89 in (48 mm)
Discrete Output Type	Relay
Contacts Type And Composition	2 C/O timed contacts, AgNi (cadmium free)
Component Name	RE48A
Time Delay Type	Asymmetrical flashing
Time Delay Range	0.2...12 min 5...300 s 0.02...1.2 s 0.5...30 min 5...300 h 0.2...12 h 0.2...12 s 0.5...30 s 2...120 s 0.05...3 s 2...120 min 5...300 min 0.5...30 h 2...120 h
[Us] Rated Supply Voltage	24...240 V AC/DC 50/60 Hz
Voltage Range	0.85...1.1 Us AC 0.9...1.1 Us DC
Line Rated Current	5 A

Complementary

Product Front Plate Size	48 x 48 mm
Control Type	Selector switch front panel
Housing Material	Self-extinguishing
Repeat Accuracy	+/- 0.2 % of the maximum setting value IEC 61812-1
Temperature Drift	+/- 0.02 %/°C of the maximum setting value IEC 61812-1
Voltage Drift	+/- 0.2 %/V of the maximum setting value 48...240 V +/- 1 %/V of the maximum setting value 24...48 V
Setting Accuracy Of Time Delay	+/- 5 % of full scale 25 °C IEC 61812-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Minimum Pulse Duration	20 ms
Reset Time	25 ms on de-energisation
Pick Up Duration	55 ms
On-Load Factor	100 %
Power Consumption In Va	1.1 VA 24 V 4.8 VA 240 V
Power Consumption In W	0.5 W 24 V 1.7 W 240 V
Breaking Capacity	1250 VA
Minimum Switching Current	100 mA
Maximum Switching Current	5 A
Maximum Switching Voltage	250 V AC/DC
Electrical Durability	100000 cycles
Mechanical Durability	30000000 cycles
Output Voltage	240 V 5 A AC-12 30 V 2 A DC-13 240 V 1.5 A AC-15
Marking	CE
Surge Withstand	1 kV differential mode IEC 61000-4-5 level 3 2 kV common mode IEC 61000-4-5 level 3
Mounting Support	Base mounted: socket Panel mounted: system supplied with the product
Local Signalling	for output relay state 1 LED (yellow) for flashing: relay energised timing in progress LED indicator (green) for on steady: relay energised, no timing in progress LED indicator (green)
Net Weight	0.31 lb(US) (0.14 kg)

Environment

Humidity Drift	+/- 0.05 %/%RH of the maximum setting value IEC 61812-1
Immunity To Microbreaks	10 ms
Dielectric Strength	1 kV 1 mA/1 minute IEC 61812-1
Protection Against Electric Shocks	4 kV class III IEC 60664-1 4 kV class III IEC 61812-1
Standards	EN 50081-1/2 EN 50082-1/2 IEC 61812-1 93/68/EEC 89/336/EEC IEC 60669-2-3 73/23/EEC
Product Certifications	UL C-tick cULus CSA
Ambient Air Temperature For Storage	-40…158 °F (-40…70 °C)
Ambient Air Temperature For Operation	-4…122 °F (-20…50 °C)
Ip Degree Of Protection	IP40 IEC 60529 housing) IP50 IEC 60529 front face)
Vibration Resistance	0.35 mm 10…55 Hz)IEC 60068-2-6
Relative Humidity	93 % without condensation IEC 60068-2-3

Resistance To Electrostatic Discharge	6 kV in contact IEC 61000-4-2 level 3 8 kV in air IEC 61000-4-2 level 3
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) 26 MHz to 1 GHz IEC 61000-4-3 level 3
Resistance To Fast Transients	2 kV IEC 61000-4-4 level 4 capacitive connecting clip) 4 kV IEC 61000-4-4 level 4 direct)
Immunity To Radioelectric Fields	10 V 0.15...80 MHz)IEC 61000-4-6 level 3
Immunity To Voltage Dips	30 % / 10 ms IEC 61000-4-11 60 % / 100 ms IEC 61000-4-11 95 % / 5 s IEC 61000-4-11
Disturbance Radiated/Conducted	Class B 0.15...30 MHz EN 55022 (EN 55011 group 1)

Ordering and shipping details

Category	US10CP222370
Discount Schedule	0CP2
Gtin	3389110649741
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.24 in (5.700 cm)
Package 1 Width	4.06 in (10.300 cm)
Package 1 Length	2.44 in (6.200 cm)
Package 1 Weight	4.62 oz (131.000 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	30
Package 2 Height	5.91 in (15.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	9.74 lb(US) (4.417 kg)

Contractual warranty

Warranty	18 months

Sustainability

Green Premium^{TM} label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency



RoHS/REACh

Well-being performance


Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings


Width 48 mm



Mounting and Clearance

Panel Cut-Out and Mounting


Panel Cut-Out



n Number of devices mounted side-by-side

Mounting


Cover positioning and mounting



e Panel thickness
1 Protective cover
2 Panel mounting frame
3 Locating screw

Connections and Schema

Wiring Diagram




Technical Description

Function L : Asymmetrical Flasher Relay (Starting Pulse Off)

Description

Repetitive cycle comprises of two, independently adjustable timing periods Ta and Tr. Each timing period corresponds to a different state of the output R.




Toff = t1 + t2 + t3
Ton = ta + tb + tc

Function Li : Asymmetrical Flasher Relay (Starting Pulse On)

Description

Repetitive cycle comprises of two, independently adjustable timing periods Ta and Tr. Each timing period corresponds to a different state of the output R.



Ton = t1 + t2 + t3
Toff = ta + tb + tc

Legend


Relay de-energised


Relay energised


Output open


Output closed

C	Control contact
G	Gate
R	Relay or solid state output
R1/R2	2 timed outputs
R2 inst.	The second output is instantaneous if the right position is selected
T	Timing period
Ta -	Adjustable On-delay
Tr -	Adjustable Off-delay
U	Supply