


ENERGIZER 387S

ZEROMERCURY

SILVER OXIDE



Industry Standard Dimensions




Specifications

Chemical System:	Silver Oxide (Zn/Ag ₂ O)
Designation:	IEC-SR42
Nominal Voltage:	1.55 Volts
Typical Capacity:	63 mAh* (to 1.2 volts)
Capacity Test:	15K ohm continuous drain at 21°C
Typical Weight:	1.1 grams (0.35 oz.)
Typical Volume:	0.25 cubic centimeters (0.02 cubic inch)
Impedance (40 Hz):	7 to 17 ohms

* Varies according to the applied load, temperature, and cutoff voltage.

Cross Section



DESIGNED FOR USE ON CONTINUOUS LOW DRAIN

Typical Discharge Characteristics

Typical Performance at 21°C (70°F)

Schedule: Continuous
Typical Drain @1.51V:
0.101 milliamperes
Load: 15K ohm




<u>Schedule</u>	<u>Typical Drains</u> at 1.51V (milliamperes)	<u>Load</u> (ohm)	<u>Cutoff</u> 1.2V (hours)
Continuous	0.101	15K	625


Temperature Characteristics

Typical Performance at Low Discharge Rates

Service Effects



Storage Effects



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.