

PRO-ELEC



INDUSTRIAL FAN HEATER

Model: PELL0527

IMPORTANT SAFETY INFORMATION

Please read these instructions carefully before use and retain for future reference.

- Check that the voltage indicated on the rating plate corresponds with that of the local network before connecting the appliance to the mains power supply.
- To avoid fire or shock hazard, plug the appliance directly into a suitable 220-240V AC electrical outlet.

DO NOT use external timer, separate remote control system, and extension cable or external adaptor with the appliance. Do not overload the supply circuit.

- This heater must not be located immediately below a socket-outlet.
- To disconnect the appliance, turn the control switch to "OFF" (Position 'O') BEFORE removing the plug from main power outlet.
- When unplugging, be sure to pull by the plug and not the cord.
- Always unplug the appliance when not in use.
- Discontinue use if plug or outlet becomes hot. It is recommended that the outlet be checked and replaced if plug or outlet is hot to touch.
- Do not abuse or damage the power cord. Fully unwind the cord before use as a coiled cord may overheat. Do not allow the supply cord to touch hot surfaces.
- DO NOT run cord under carpeting. DO NOT cover cord with throw rugs, runners, or the like. Position the cord away from traffic area and where it will not cause a trip hazard.
- DO NOT operate the appliance with a damaged cord or plug, or after the appliance malfunctions, has been dropped or damaged in any manner.
- If the supply cord is damaged DO NOT attempt to service this appliance yourself. Return it to a qualified service agent for mechanical adjustment, or repair.
- Ensure that the supply cord is kept away from heat or sharp edges that could cause damage.
- DO NOT insert or allow foreign objects to enter any ventilation or exhaust vent opening as this may cause an electric shock or fire, or damage to the appliance.


WARNING: In order to avoid overheating, **DO NOT COVER** the heater.

- To prevent a possible fire, DO NOT block air intakes or exhaust vents in any manner. DO NOT use on soft surfaces, where openings may become blocked.
- DO NOT move the appliance when it is operating. Only move the appliance when cool.
- The appliance is hot when in use. To avoid burns, DO NOT touch any hot surfaces. Keep combustible materials, such as furniture, pillows, bedding, papers, clothes, and curtains at least 3 ft (0.9 m) from the front of the heater and keep them away from the sides and rear.
- This appliance is not intended for use by persons (INCLUDING CHILDREN) with reduced physical, sensory or mental capabilities, or lack of experience and knowledge, unless they have been given supervision or instruction concerning use of the appliance by a person responsible for their safety.
- Children should be supervised to ensure that they do not play with the appliance.
- Do not use this heater in the immediate surroundings of a bath or a shower.
- This appliance is not intended for use in bathrooms, laundry areas and similar indoor location where this it may come in contact with water.
- Do not immerse any part of this appliance or supply cord in water.
- DO NOT use in areas where gasoline, paint, or flammable liquids are used or stored.
- This appliance is designed for indoors ONLY.

ADJUSTMENT

- The heater has a small angle of adjustment that can be set by the user.
- Loosen the thumbwheels on both sides of the heater
- Tilt the heater as required.
- Tighten the thumbwheels before use.


OPERATION



Controls

NOTE: The heater may emit a small amount of smoke and odour when used for the first time. This is normal and caused by the lubricant protection on the heating element during the production process.

WARNING: Do not leave the appliance switched on and unattended at any time.

- The heater has two settings: “Fan only” and “Heat”.
- The “Fan” setting has no heating and just provides ventilation.
- Turn the dial to “” for heating.

REGULATING THE THERMOSTAT

- If the heater switches off before the room reaches the desired level, turn the thermostat clockwise to increase the temperature setting.
- Turn the thermostat control counter clockwise to decrease the setting.
- The heating element will turn on or off under thermostatic control to maintain this temperature and the fan will continue operating.
- It is recommended to switch to fan only setting and allow the fan to cool the heater down for 2 minutes before turning the device off completely.
- Turn the left hand dial to “O” to switch the heater off completely.

NOTE: There is an additional internal self-resetting safety cutout that cuts power to prevent overheating should it occur.

CLEANING & MAINTENANCE

- Always remove the plug from the socket-outlet and allow the heater to cool down before cleaning it.
- Clean the air inlet/outlet grilles frequently, using a soft, dry cloth, to prevent dust building up.
- Do not use any chemicals, abrasives or solvents that may damage the heater.
- To store the heater, place it in a clean, dry environment, ensuring it is protected from dust.

SPECIFICATIONS

Model	PELL0572
Rated Voltage	220-240VAC
Frequency	50Hz
Rated Power	2000W 8.3~9.1A
Dimensions (mm)	285 x 230 x 340
Weight	3.8Kg
IP Rating	IP24
Heat Output	
Nominal heat output P_{nom}	2.0kW
Min heat output P_{min}	0kW
Max heat output P_{max}	2,0kW
Auxiliary electricity consumption	
At nominal heat output $e_{l_{max}}$	0kW
At minimum heat output $e_{l_{min}}$	0kW
In standby mode $e_{l_{sb}}$	N/A
With mechanical thermostat room temperature control	YES

NEVER LEAVE THE HEATER UNATTENDED WHEN IT IS IN USE

DO NOT disassemble this appliance as there are no user serviceable parts inside.
Any attempt to do so will void any warranty.



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT

When this product has reached the end of its life it must be treated as Waste Electrical & Electronics Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

As is typical for all portable heaters -
This product is only suitable for well insulated spaces or occasional use.

Made in China
PO Box 13362 Dublin 2
PR2 9PP
Man Ref 1.0