

CHERRY STREAM MOUSE COMFORT

WIRELESS MOUSE



Models may vary from the image shown

The silent click mouse with ergonomic shape and wireless freedom.

With the STREAM MOUSE COMFORT you experience working comfort at the highest level - with the innovative and ergonomic mouse technology, user-friendly design and wireless freedom merge into a faithful companion that lives up to your needs!

Dreamteam features: Ergonomics and wireless freedom

The cordless right-hand mouse is the optimal solution for comfortable and efficient working. With state-of-the-art 2.4 GHz wireless technology and a generous range of up to 10 m, you can remain flexible all the time in your workplace.

The ergonomic wireless mouse is specifically designed for right-handed people with medium to large hands. Every aspect of its design aims to promote a natural and relaxed hand posture. The high-quality metal scroll wheel not only lends an elegant appearance, but also ensures a correspondingly high-quality tactile experience. The handy thumb rest with the attractive Voronoi pattern offers a pleasant feel and gives the mouse a touch of elegance. Your thumb is also very comfortable and relieved. The generous sliding surfaces on the underside significantly reduce friction, which makes the mouse extremely smooth and easy to navigate over all surfaces.

Sophisticated technology meets comfort while working: Relaxed and efficient throughout the working day!

With the CHERRY STREAM MOUSE COMFORT you experience absolute precision with every movement – with a resolution of up to 4000 dpi, the large computer mouse enables exact control. Thanks to the innovative and 4-step adjustable dpi switch, you

can adjust the sensitivity to your individual requirements in no time at all.

Thanks to the clever dongle holder on the back, the stylish yet minimalistic wireless mouse makes searching for the receiver a thing of the past. Thanks to the battery life of up to 16 months, the optical mouse guarantees particularly long-lasting use. A flashing LED on the top signals in good time when a battery change is required, while the on/off switch helps extend the battery life. This means you can stay in control of your workflow without worrying about unexpected interruptions.

The perfect balance: Practical benefits and individuality

The front and back buttons on the side are extremely useful in everyday use. With a single click, you can easily switch between digital content or actions for intuitive and smooth operation. These features make it easier to focus on the essentials. In addition, the free CHERRY KEYS software offers the possibility to adapt the mouse settings according to individual needs and thus offers additional advantages for an optimal user experience.

The STREAM MOUSE COMFORT seamlessly combines comfort, design and efficiency. It is the ideal choice for demanding users who are looking for a companion which combines ergonomics, design and efficiency.

Decisive Advantages

- Ergonomic 6-button mouse for right-handed users
- Undisturbed working with whisper-quiet mouse buttons
- Fatigue-free working thanks to rubberized thumb pad with modern Voronoi pattern
- High-quality metal mouse wheel ensures durability, a pleasant feel and precise scrolling
- Interference-free 2.4 GHz wireless technology with a range of up to 10 meters
- Highly precise sensor with resolution adjustable in four stages up to 4000 dpi
- AES-128 encryption
- Integrated battery status display and up to 16 months battery life
- Generous glide pads for effortless navigation on all surfaces
- Nano USB receiver and simple plug & play start up
- GS approval

CHERRY STREAM MOUSE COMFORT

WIRELESS MOUSE

Technical specifications

Mouse

- Resolution: 1000/2000/3000/4000 dpi (switchable)
- Sensor: Optical (PixArt)
- Number of buttons: 6
- Design: Right-handed design

Weights

Mouse:	approx. 123 g
Receiver:	approx. 3 g
Total weight (with packaging):	approx. 208 g

Range

Wireless: approx. 10 m

Batteries

1 x AA

Connection

USB-A (dongle)

Product approvals

- CE
- UKCA
- FCC
- China RoHS
- Windows hardware compatibility
- GS

System requirements

USB port (type A)

Scope of delivery

- Mouse
- USB receiver
- Battery (1 x AA inserted in the device)
- Operating Manual

Dimensions

Mouse:	approx. 126.7 x 85.2 x 49.7 mm
Receiver:	approx. 19 x 14.5 x 6.5 mm
Packaging:	approx. 135 x 92 x 59 mm

Storage Temperature

-20°C to 65°C, max. 85% humidity

Operating temperature

0°C to 50°C, max. 85% humidity

Packaging unit

Number of products in outer package: 10
Number of outer packages per pallet: 140

Errors excepted. We reserve the right to make technical changes and changes to delivery options. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Actual battery life is strongly depending on individual user behavior and hardware setup.

Design variants

	Product name	Order number	Color	EAN/UPC code
1	CHERRY STREAM MOUSE COMFORT	JW-8550-2	Black	4025112110603 840183607524
2	CHERRY STREAM MOUSE COMFORT	JW-8550-0	White-gray	4025112110597 840183607517 (UPC)

Please contact your local CHERRY Service and Support team or your CHERRY sales partner to find out which versions are available in your country.